







SECTION A-A

N = Number of poles

Dim L = N x 5.0 + 1.5

Dim P = (N - 1) x 5.0

	Dim L	Dim P
1-6p	±0.15	±0.15
7-12p	±0.25	±0.25
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

△

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.09.19	The description in drawing is revised	Jacke

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item a Terminal lever: Thermoplastic (UL94 V-0)
- Item b Terminal body: Thermoplastic (UL94 V-0)
- Item c Terminal cover: Thermoplastic (UL94 V-0)
- Item d Solder pin: Brass Tin plated
- Item e Spring clamp: Stainless steel

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG): 16-20
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ± 10°C / 5 Sec
- Safety Approval: cULus

NE xx 0 0 x 0 xxxx G

01 1 pole
02 2 poles
03 3 poles
...
24 24 poles

0 Black
5 Green
6 Blue
8 Grey

any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NE 5.0mm series							
PART NO.	NExx00x0xxxxG				DWG NO.	8NE0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacke 2009.09.19	Jacke 2009.09.19				UNIT: mm	X. ±0.50
							SCALE: 4/1	X.X ±0.30
				SHEET: 01/01	REV.: C		X.XX ±0.10	
							X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>NE0200800000G</u>	<u>NE0300800000G</u>	<u>NE0400800000G</u>	<u>NE0500800000G</u>	<u>NE0600800000G</u>	<u>NE0700800000G</u>
<u>NE0800800000G</u>	<u>NE0900800000G</u>	<u>NE1000800000G</u>	<u>NE1100800000G</u>	<u>NE1200800000G</u>	<u>NE1300800000G</u>
<u>NE1400800000G</u>	<u>NE1500800000G</u>	<u>NE1600800000G</u>	<u>NE1700800000G</u>	<u>NE1800800000G</u>	<u>NE1900800000G</u>
<u>NE2000800000G</u>	<u>NE2100800000G</u>	<u>NE2200800000G</u>	<u>NE2300800000G</u>	<u>NE2400800000G</u>	