




SIGN	DATE	DESCRIPTION	APPROVER
△	07/22`13	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item a Clamp: Brass(Cuzn) Ni plated
- Item b Terminal screw: Steel Zinc plating;"- "slot type
- Item c Female contact: PhBz
- Item d Terminal(housing): Thermoplastic (UL94 V-0)

Electrical

- Voltage rating: 150VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque(Lb-In): 1.1
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension:

EHxx21x0xxxxG

Poles		G RoHS compliant (lead<4%) In copper Alloy
02 2Contacts		
03 3Contacts		
...		
24 24Contacts	0 Black (RAL9005)	0000 Standard @ Logo
	2 Red (RAL3001/D)	000A Standard ANY Logo
	3 Orange(RAL2011/P)	Any special item by customer request,
	4 Yellow(RAL1018/A)	please contact sales department.
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

N = Number of poles
Dim A=Nx3.5
Dim B=(N-1)x3.5

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.25	±0.25
19-24p	±0.30	±0.25

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EH - 3.5mm Series						DWG NO.		8EH0001	
PART NO.		EHxx21x0xxxxG				DWG NO.		8EH0001			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance			
			Chen Bo 09/12`13	Chen Bo 09/12`13				UNIT: mm		X.	±0.50
						SCALE: NONE		X.XX		±0.10	
						SHEET: 01/01		REV.: D		X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>EH0221600000G</u>	<u>EH0321600000G</u>	<u>EH0421600000G</u>	<u>EH0521600000G</u>	<u>EH0621600000G</u>	<u>EH0721600000G</u>
<u>EH0821600000G</u>	<u>EH0921600000G</u>	<u>EH1021600000G</u>	<u>EH1121600000G</u>	<u>EH1221600000G</u>	<u>EH1321600000G</u>
<u>EH1421600000G</u>	<u>EH1521600000G</u>	<u>EH1621600000G</u>	<u>EH1721600000G</u>	<u>EH1821600000G</u>	<u>EH1921600000G</u>
<u>EH2021600000G</u>	<u>EH2121600000G</u>	<u>EH2221600000G</u>	<u>EH2321600000G</u>	<u>EH2421600000G</u>	<u>EH0621500000G</u>
<u>EH0421500000G</u>	<u>EH0821500000G</u>	<u>EH0321500000G</u>	<u>EH0221500000G</u>		