

SIGN	DATE	DESCRIPTION	APPROVER
△	7/07'09	Electrical standard is changed from UL/cUL to cULus	Kind
△	7/07'09	Current rating changed from 8A to 10A	Kind
△	7/07'09	Operating tem. changed from -30°C~105°C to -40°C~115°C	Kind
△	7/07'09	Add VDE Certification	Kind
△	2/03'12	Add the Elevation view	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

### Material


- (A) Terminal body(metal housing of double): Brass(CuZn),Ni plated
- (B) Terminal body(metal housing of single ): Brass(CuZn),Ni plated
- (C) Terminal screw: Steel Zinc plating "-" slot type
- (D) Wire guard: Steeless steel
- (E) Insulator (lever): Thermoplastic (UL94V-0)
- (F) Insulator (housing): Thermoplastic (UL94V-0)


- △ 8 △ 5 Electrical cULus VDE
- Voltage rating: 400VAC / 450VAC
- △ 6 ● Current rating: 10A / 24A
- Wire range: 0.34~2.5mm<sup>2</sup>
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque(Lb-In): 3.5 /0.5
- Screw: M3 /Nm
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.8KV / 2.5KV
- △ 7 ● Operating temperature: -40°C to +115°C
- Safety Approval: cULus VDE
- Critical dimension: △




# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TM - series 3 Poles					
PART NO.	TM0319000000G			DWG NO.	8TM0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			Chen Bo 02/03'12		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: G		X.XX ±0.10
SHEET: 01/01				X° ±1°			





SIGN	DATE	DESCRIPTION	APPROVER
△	7/07'09	Electrical standard is changed from UL/cUL to cULus	Kind
△	7/07'09	Current rating changed from 8A to 10A	Kind
△	7/07'09	Operating tem. changed from -30°C~105°C to -40°C~115°C	Kind
△	7/07'09	Add VDE Certification	Kind
△	6/14'10	Current rating changed from 10A to 12.5	Chen Bo
△	2/03'12	Add the Elevation view	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

# Material

- (A) Terminal body(metal housing of double): Brass(CuZn),Ni plated
- (B) Terminal body(metal housing of single ): Brass(CuZn),Ni plated
- (C) Terminal screw: Steel Zinc plating "-" slot type
- (D) Wire guard(short): Steeless steel
- (E) Insulator (lever): Thermoplastic (UL94V-0)
- (F) Insulator (housing): Thermoplastic (UL94V-0)
- (G) Wire guard(Long): Steeless steel

- △ 10 △ 7 Electrical cULus VDE
  - Voltage rating: 400VAC / 450VAC
- △ 8 ● Current rating: 10A / 24A
  - Wire range: 0.34~2.5mm<sup>2</sup>
  - Solid wire(AWG): 14-22
  - Stranded wire(AWG): 14-22
  - Torque(Lb-In): 3.5 /0.5 Nm
  - Screw: M3
  - Wire strip length: 7-8mm
  - Withstanding Voltage: 1.8KV / 2.5KV
- △ 9 ● Operating temperature: -40°C to +115°C
  - Safety Approval: cULus VDE
  - Critical dimension: △

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TM - series 5 Poles with handle			
PART NO.	TM0519000000G			DWG NO.	8TM0301
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
			Chen Bo 02/03'12		Tolerance
					X. ±0.50
					X.X ±0.30
				UNIT: mm	X.XX ±0.10
				SCALE: NONE	X° ±1°
				SHEET: 01/01	REV.: H

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TM0319000000G](#) [TM0419000000G](#) [TM0519000000G](#)