

NOTES:

1. MATERIALS AND FINISHES:

SMA CRIMP PLUG - P/N: 132114
BNC CRIMP PLUG - P/N: 112132
CABLE - RG-316/U COAXIAL CABLE



2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL

3. PACKAGING:

A. QUANTITY: SINGLE PACK
B. BAG TO BE MARKED: AMPHENOL RF, 245101-01-XX.XX, AND DATE CODE

245101-01-XX.XX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	09-Jun-10	--	CL
	B	SEE SHEET 1	27-Mar-14	2715	MB/BCG



DESIGN REQUIREMENTS:

☒ FREQUENCY: DC TO 3.0 GHz

☐ VSWR _____ : 1 MAX

☐ INS. LOSS _____ dB MAX

☒ CONTINUITY

☒ HI-POT : 500 VRMS

☐ OTHER

ORDERING INFORMATION		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH IN INCHES * [METERS]
245101-01-06.00	-	6.00 [0.152]
-	245101-01-M0.25	9.84 [0.250]
245101-01-12.00	-	12.00 [0.305]
245101-01-18.00	-	18.00 [0.457]
-	245101-01-M0.50	19.69 [0.500]
245101-01-24.00	-	24.00 [0.610]
-	245101-01-M0.75	29.53 [0.750]
245101-01-36.00	-	36.00 [0.914]
-	245101-01-M1.00	39.37 [1.000]
245101-01-48.00	-	48.00 [1.219]

* ADDITIONAL LENGTHS CAN BE PROVIDED.
CONTACT AMPHENOL RF MARKETING FOR QUOTE

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°			MATERIAL SEE NOTES	DRAWN MOHAN	DATE 14-Mar-14	TITLE SMA CRIMP PLUG TO BNC CRIMP PLUG,USING RG-316/U COAXIAL CABLE VARIOUS LENGTHS		Amphenol Connex	
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.				ENGINEER MOHAN	DATE 14-Mar-14				
			REFERENCE			APPROVED B.C. GLEISSNER	DATE 27-Mar-14		
						CAD FILE		DWG SIZE B	DRAWING NO. 245101-01-XX.XX
							SCALE: 3.0:1	SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[245101-01-06.00](#) [245101-01-12.00](#) [245101-01-24.00](#) [245101-01-36.00](#) [245101-01-48.00](#) [245101-01-M0.25](#)
[245101-01-M0.50](#) [245101-01-M0.75](#) [245101-01-M1.00](#) [245101-01-18.00](#)