




REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
01	-	CUSTOMER DRAWING	-	-	-



NOTES:

1) CONTACT BARREL RANGE: 16AWG TO 18AWG

2) RECOMMENDED CRIMP TOOLS:

HAND CRIMPER: MFX-3959

PNEUMATIC CRIMPER: MFX-3960

3) EXTRACTION TOOL: QXRT16

4) MATERIALS:

HOUSING BODY: ZINC DIE CAST, NICKEL PLATED

INSULATION INSERT: PA66, UL94/V-0

CONTACT: BRASS, GOLD FLASH PLATED

SEAL AND O-RING: NBR (NITRILE BUTADIENE RUBBER)

5) ELECTRICAL DATA:

a) CURRENT (MAX): 13A

b) VOLTAGE (MAX): 250V AC/DC

c) INSULATION RESISTANCE (MIN): 5000M OHMS

d) TEST VOLTAGE (BETWEEN CONTACTS): 3050V

6) TECHNICAL DATA:

a) TEMPERATURE RANGE: -40°C TO 105°C

b) PROTECTION: IP67 (MATED CONDITION)

c) MATING CYCLES: >500


d) VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204

e) THERMAL SHOCK PER MIL-STD-202 METHOD 207

f) 48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101

7) RoHS COMPLIANT

ILLUSTRATION: COMPLETE KIT



8	MP16M23F	CONTACT, PIN, SIZE 16	2
1	RT07128PNH	CONNECTOR	1
QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE
1) All dimensions are in metric(mm).	DRAWN:	MRF
2) Tolerances are as follows:	1 PL DEC ± 0.30	10SEP13
	2 PL DEC ± 0.15	Fractions $\pm 1/64$
	3 PL DEC ± 0.08	Angles $\pm 1^\circ$
3) Note reference =	CHECKED:	
	ENGINEER:	
	APPROVAL:	
	CUSTOMER:	
PROCESS SPECIFICATIONS:		
NEXT ASSY:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.
SIZE	TYPE	DWG NO:
B	C-	RT07128PNH-K
REVISION		01
SCALE:	NONE	SHEET 1 OF 1

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

KIT, ECO-MATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RT07128PNH-K](#)