

NOTES:


1. MATERIALS AND FINISHES:  
BODIES - BRASS, GOLD PLATING  
CONTACT - BERYLLIUM COPPER, GOLD PLATING  
INSULATOR - PTFE
2. ELECTRICAL:  
A. IMPEDANCE: 75 OHM  
B. FREQUENCY RANGE: DC - 3 GHz  
C. RETURN LOSS : -30 dB MIN AT 3 GHz
3. MECHANICAL:  
A. DURABILITY: 500 CYCLES MIN.  
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:  
A. QUANTITY: SINGLE PACK  
B. MARKING: BAG TO BE MARKED  
"AMPHENOLRF, APH-HDBNCJ-T, AND DATE CODE"

THIRD ANGLE PROJ.




REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	14-Oct-10	48098	NMV



SCALE 4.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm    0.5 - 6mm ± 0.1mm    6 - 30mm ± 0.2mm    30 - 120mm ± 0.3mm    ANGLES ± 1°	MATERIAL	DRAWN S.LI	DATE 14-Oct-10	TITLE HD-BNC, JACK TERMINATION		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
	SEE NOTES	ENGINEER BALAJI M	DATE 11-Mar-10				
	REFERENCE EAR # 3968	APPROVED S.HSIEH	DATE 15-Oct-10				
	CONFIGURATION LEVEL: =%%Z0HXIBIGC%=	CAD FILE	Root Folder/HD-BNC/APH-HDBNCJ-T	SCALE: 11.5:1.0	SHEET 2 OF 2	DRAWING NO.APH-HDBNCJ-T	
	FINISH			DWG SIZE B	REV A	ITEM NO.APH-HDBNCJ-T	
						PART NO.APH-HDBNCJ-T	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[APH-HDBNCJ-T](#)