



REV.	DATE	ECR NO.	DESCRIPTION
NC	03/24/09	—	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED CONTACT PIN HEX CRIMP SIZE .068" [1.73]
2. MAX. PANEL THICKNESS= 3.5mm

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex						
8	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN	GRS	03/24/09									
7	LOCK WASHER	BRASS	NICKEL	1			CHECKED					PART DESCRIPTION TNC REVERSE POLARITY BULKHEAD DIRECT SOLDER JACK (FOR .085”, .086” CABLE)						
6	GASKET	RUBBER	RED	1			ISSUED											
5	INSULATOR	PTFE	NATURAL	1			SHEET	1 OF 1				PART NO. 122400RP–10						
4	CONTACT PIN	BRASS	GOLD	1														
3	INSULATOR	PTFE	NATURAL	1									DWG. NO. 122400RP–10.DWG					
2	BARREL	BRASS	NICKEL	1													REV. NC	
1	BODY	BRASS	NICKEL	1														
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE		C:/122/122400RP–10.DWG									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122400RP-10](#)