

# Metral® High Speed 4000 Series Backplane Connector

## ENHANCED FUTUREBUS+ SUPPORT UP TO 6.25G FOR HIGH SPEED APPLICATIONS

Amphenol ICC's Metral® 4000 Series is a high-speed 2mm backplane connector system consisting of right-angle receptacles and vertical headers. The 4000 Series features a unique stripline structure in both the receptacle and header. Compared to the Metral® 1000 and 2000 Series, Metral® 4000 receptacle connectors employ a modified receptacle contact geometry optimized for 100Ω differential signals.

This yields a better impedance match and lower insertion loss. The headers and receptacles use a press-fit pin designed for 0.60mm drilled holes. The system is designed to conveniently stack end-to-end with other Amphenol ICC Metral® products.

- Data rate: 6.25Gb/s
- Dedicated ground rows in addition to ground shields between columns
- Meets IEEE Futurebus+ standard
- Available in Press-fit and 5x6 module size

### FEATURES

- Fully shielded strip-line transmission structure for receptacles and headers
- Stackable end-to-end with other Amphenol ICC Metral® products
- Optimized contact geometry
- Available in 5-row configurations for receptacles and 5/8-row configuration for headers
- Press-fit headers and receptacles
- Smaller Press-fit PCB hole diameter
- Dual-beam receptacle contacts
- Various header loading patterns
- 25 pairs/inch in 5-row connector
- 100 mating cycles
- Lead free and RoHS compliant



### TARGET MARKETS



### BENEFITS

- Reduced crosstalk & improved signal performance (less than 5% multi-line active NEXT @ 100ps rise time in differential applications)
- Supports blind mating
- Support different applications
- Meets V-by-One HS standards
- Suitable for automotive application
- Better routing and lower via capacitance
- Provides electrical reliability and withstands vibration
- Allows customized selection
- High contact density
- Better durability
- Meets health, safety and environment requirements

## TECHNICAL INFORMATION

### MATERIAL

- Housings: High-temperature, glass filled LCP, UL94V-0
- Receptacle Contacts: Copper alloy
- Header Pins: Copper alloy
- Ground Shields: Copper alloy
- Plating:
  - Contact Area: per Telcordia™ GR-1217-core for Central Office and Uncontrolled Environment
- Press-fit Tails: Matt tin

### ELECTRICAL PERFORMANCE

- Current Rating: 1A when all contacts are powered or 3A when one contact is powered at a 30°C max. temperature rise
- Contact Resistance: 40mΩ max.
- Insulation Resistance: 1000MΩ min.
- Signal Integrity: Data and SPICE models are available at [www.fci.com](http://www.fci.com)

### MECHANICAL PERFORMANCE

- Mating Force: 0.55N max. per contact pair including ground and shield contacts
- Withdrawal Force: 0.20N min. per contact pair including ground and shield contacts

### ENVIRONMENTAL

- Operating Temperature: -65°C to +105°C

### SPECIFICATIONS

- IEC 61076-4-104
- Product Specification: GS-12-184
- Application Specifications
  - GS-20-014 for headers
  - GS-20-017 for receptacles

### PACKAGING

- Tubes

### TARGET MARKETS/APPLICATIONS



Transmission  
Access  
Switches  
Routers



Servers  
Storage enclosures



Rack-based Systems

## PART NUMBERS

Number of Rows & Positions	Daughter Card Thickness	Header	Part Numbers
5-Row 5x6	1.27mm (0.050in.) – 2.54mm (0.100in.)	55003-XXXXXX	52057-XXX
5-Row 5x6	2.54mm (0.100in.) – 3.40mm (0.134in.)	59569-XXXXXX	52062-XXX

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## FCI / Amphenol:

[55003-101003LF](#) [52057-302LF](#) [52062-302LF](#) [52062-302](#) [55003-101002LF](#) [55003-101004LF](#) [55004-102001LF](#)  
[55004-102002LF](#) [59566-1001LF](#) [59567-1003LF](#) [59569-101001LF](#) [59569-101002LF](#) [59566-1005LF](#) [59566-1002LF](#)  
[59566-5003LF](#) [59567-1004LF](#) [59566-1006LF](#) [59566-1007LF](#) [52057-102LF](#) [55003-501003LF](#) [52062-102LF](#) [55003-](#)  
[301003LF](#) [55003-101005LF](#) [59568-5001LF](#) [55003-301002LF](#) [52057-202LF](#) [52062-202LF](#) [55003-201002LF](#) [55003-](#)  
[201003LF](#) [55003-201004LF](#) [55003-201005LF](#) [59566-2007LF](#) [59567-2003LF](#) [59567-2004LF](#) [59569-201001LF](#)  
[59569-201002LF](#) [55004-202001LF](#) [55004-202002LF](#) [59566-2001LF](#) [59566-2002LF](#) [59566-2005LF](#) [59566-2006LF](#)  
[10125034-201LF](#) [10130513-201LF](#) [10139370-201LF](#)