




REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JUN-20-2014	BEN	TOMMY



11/16-24 UNEF THREAD



- NOTES : (UNLESS OTHERWISE SPECIFIED)**
- MATERIAL :**
 - METAL NUT : AL ALLOY , NICKEL PLATED.**
 - GASKET : SILICONE RUBBER.**
 - METAL CLIP : STAINLESS STEEL.**
 - BACK SHELL : ZINC ALLOY, NICKEL PLATED.**
 - EMI SHIELDING RING : STAINLESS STEEL.**
 - O-RING : SILICONE RUBBER.**
 - GROMMET : RUBBER.**
 - CLAMP INSERT : THERMOPLASTIC UL94 V-0.**
 - END NUT : ZINC ALLOY , NICKEL PLATED.**
 - ROHS COMPLIANT.**
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.**

P/N	SHIELDING RING	CABLE RANGE
RT0B-12CG-C1	WITHOUT	Ø6-Ø10.5mm
RT0B-12CG-C2	WITHOUT	Ø8.5-Ø12.5mm
RT0B-12CG-S1	WITH	Ø6-Ø10.5mm
RT0B-12CG-S2	WITH	Ø8.5-Ø12.5mm

QUANTITY		PART NUMBER		DESCRIPTION		ITEM
MATERIALS LIST						
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.15 Angles ±1° 3 PL DEC ±0.08 3) Note reference =		SIGNATURES DATE DRAWN: BEN JUN-20-2014 CHECKED: ENGINEER: APPROVAL:		 Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036		
MATERIAL SPECIFICATIONS:		CUSTOMER:		ECO-MATE,ANGLE 90°, CORD GRIP,SIZE 12		
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		SIZE	TYPE	DWG NO.
NEXT ASSY:				B	C-	RT0B-12CG-xx
				SCALE	NONE	
				SHEET	1	OF 1

TITLE: ECO-MATE,ANGLE 90° CORD GRIP,SIZE 12
DWG NO.: RT0B-12CG-xx
REV: B1
SH: 1
OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RT0B-12CG-S2](#) [RT0B-12CG-S1](#)