




REVISIONS																																																			
REV	ECO	DESCRIPTION		DATE	BY																																														
01	-	CUSTOMER DRAWING		-	-																																														
TITLE: KIT, ECO-MATE DWG NO: D101																																																			
 <p>ASSEMBLED VIEW</p>																																																			
 <p>WAVE SPRING COUPLING NUT HOUSING BODY O-RING INSULATION INSERT 9/16-24 UNEF THREAD</p>																																																			
<p>NOTES:</p> <ol style="list-style-type: none"> 1) CONTACT BARREL RANGE: 20AWG TO 22AWG 2) RECOMMENDED CRIMP TOOLS: HAND CRIMPER: MFX-3959 PNEUMATIC CRIMPER: MFX-3960 3) EXTRACTION TOOL: QXRT20 4) MATERIALS: HOUSING BODY: ZINC DIE CAST, NICKEL PLATED INSULATION INSERT: PA66, UL94/V-0 CONTACT: BRASS, GOLD FLASH PLATED SEAL AND O-RING: NBR (NITRILE BUTADIENE RUBBER) 5) ELECTRICAL DATA: a) CURRENT (MAX): 7.5A b) VOLTAGE (MAX): 150V AC/DC c) INSULATION RESISTANCE (MIN): 5000M OHMS d) TEST VOLTAGE (BETWEEN CONTACTS): 1500V <p>7) TECHNICAL DATA:</p> <ol style="list-style-type: none"> a) TEMPERATURE RANGE: -40°C TO 105°C b) PROTECTION: IP67 (MATED CONDITION) c) MATING CYCLES: >500 d) VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204 e) THERMAL SHOCK PER MIL-STD-202 METHOD 207 f) 48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101 <p>8) RoHS COMPLIANT</p>																																																			
 <p>ILLUSTRATION: COMPLETE KIT</p>																																																			
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>QUANTITY</th> <th>PART NUMBER</th> <th>DESCRIPTION</th> <th>ITEM</th> </tr> </thead> <tbody> <tr> <td>6</td> <td>MP20W23F</td> <td>CONTACT, PIN, SIZE 20</td> <td>3</td> </tr> <tr> <td>1</td> <td>RTOL-10CG-S1</td> <td>CORD GRIP</td> <td>2</td> </tr> <tr> <td>1</td> <td>RTOW6106PNH</td> <td>CONNECTOR</td> <td>1</td> </tr> </tbody> </table> <p>MATERIALS LIST</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="3" style="text-align: center;">UNLESS OTHERWISE SPECIFIED</td> </tr> <tr> <td colspan="3">1) All dimensions are in metric(mm).</td> </tr> <tr> <td colspan="3">2) Tolerances are as follows:</td> </tr> <tr> <td colspan="3">1 PL DEC ± 0.30 Fractions $\pm 1/64$</td> </tr> <tr> <td colspan="3">2 PL DEC ± 0.15 Angles $\pm 1^\circ$</td> </tr> <tr> <td colspan="3">3 PL DEC ± 0.08</td> </tr> <tr> <td colspan="3">3) Note reference = </td> </tr> <tr> <td colspan="3">MATERIAL SPECIFICATIONS:</td> </tr> <tr> <td colspan="3">PROCESS SPECIFICATIONS:</td> </tr> <tr> <td colspan="3">NEXT ASSY:</td> </tr> </table> <p style="text-align: right;">Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036</p> <p style="text-align: right;">KIT, ECO-MATE</p>						QUANTITY	PART NUMBER	DESCRIPTION	ITEM	6	MP20W23F	CONTACT, PIN, SIZE 20	3	1	RTOL-10CG-S1	CORD GRIP	2	1	RTOW6106PNH	CONNECTOR	1	UNLESS OTHERWISE SPECIFIED			1) All dimensions are in metric(mm).			2) Tolerances are as follows:			1 PL DEC ± 0.30 Fractions $\pm 1/64$			2 PL DEC ± 0.15 Angles $\pm 1^\circ$			3 PL DEC ± 0.08			3) Note reference = 			MATERIAL SPECIFICATIONS:			PROCESS SPECIFICATIONS:			NEXT ASSY:		
QUANTITY	PART NUMBER	DESCRIPTION	ITEM																																																
6	MP20W23F	CONTACT, PIN, SIZE 20	3																																																
1	RTOL-10CG-S1	CORD GRIP	2																																																
1	RTOW6106PNH	CONNECTOR	1																																																
UNLESS OTHERWISE SPECIFIED																																																			
1) All dimensions are in metric(mm).																																																			
2) Tolerances are as follows:																																																			
1 PL DEC ± 0.30 Fractions $\pm 1/64$																																																			
2 PL DEC ± 0.15 Angles $\pm 1^\circ$																																																			
3 PL DEC ± 0.08																																																			
3) Note reference = 																																																			
MATERIAL SPECIFICATIONS:																																																			
PROCESS SPECIFICATIONS:																																																			
NEXT ASSY:																																																			
SIZE	TYPE	DWG NO:	REVISION																																																
B	C-	RTOW6106PNH-K	01																																																
SCALE: NONE			SHEET 1 OF 1																																																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RT0W6106PNH-K](#)