

Minitek MicroSpaceXS™ Waterproof 1.27mm Crimp-to-Wire Connector Platform

COMPACT, ROBUST AND VERSATILE CONNECTOR SYSTEM

Minitek MicroSpace XS™ Waterproof Crimp-to-Wire connector platform's unique design is compatible to LV214 Severity-3 and USCAR-T2V2 specifications. These 1.27mm pitch connectors come with a current rating up to 3A per contact making ideal for higher power applications. Minitek MicrospaceXS™ connectors are available in staggered vertical and horizontal configuration with, PIP soldering, and tin or gold plating.

- LV214 Severity-3 and USCAR-T2V2 compatible
- Terminal Positioning Assurance (TPA)
- Primary and secondary contact retention
- Connector Positioning Assurance (CPA)



TARGET MARKETS



FEATURES

- Mechanical Connector Position Assurance (CPA)
- Terminal Position Assurance (TPA)
- Poka-Yoke polarization and color coding
- Current rating up to 3A per contact
- 4N normal force for vibration > 75N connector locking strength

BENEFITS

- Ensures proper mating of header and receptacle and avoids unintentional trigger of the latch
- Ensures proper terminal insertion position and retention
- Prevents visual mismatch
- Meets higher power performance requirements
- High vibration and locking resistance

TECHNICAL INFORMATION

MATERIAL

- Contact: High current alloy with optional tin and gold/GXT plating
- Housing: High temperature thermoplastic, UL94V-0
- Platings:
 - Tin (Sn): 3μ
 - Gold (Au): 0.76μ

ELECTRICAL PERFORMANCE

- Current Rating: 3A
- Voltage Rating: 48V
- Low Level Contact Resistance: <25mΩ
- Insulation Resistance: >100mΩ
- Dielectric Withstanding Voltage: 500VAC
- Temperature Rise: 30°C max.

MECHANICAL PERFORMANCE

- Terminal Insertion Force/Terminal: <3N
- Low Insertion Force Terminal:(<2N) available upon request
- Terminal Retention into Housing: >50N
- Durability:
 - 20 mating cycles for Sn
 - 100 mating cycles for Au/GXT

ENVIRONMENTAL

- Operating Temperature: -40°C to +130°C
- IP68
- UL94V-0

APPROVALS AND CERTIFICATIONS

- LV214 Severity-3
- USCAR-T2V2
- VW75174 – Slow Motion Bending Test
- VW60330 – Crimp specification

SPECIFICATIONS

- Product Specification: GS-12-1465
- Packaging Specification: GS-14-2222

PACKAGING

- PCB Header: Tube
- Receptacle Housing: Bag
- Terminal: Reel

TARGET MARKETS/APPLICATIONS



Lighting
Camera / Sensor
Infotainment
HVAC
Battery Management



Automotive Lighting

PART NUMBERS

Description	Part Numbers
Minitek MicroSpaceXS™ Waterproof Header	10155466
Minitek MicroSpaceXS™ Waterproof Receptacle	10155470
Minitek MicroSpaceXS™ Terminals	10155447

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[T2012-24](#) [T2011-22](#) [10155466-A108ULF](#) [T3014-26](#) [T1013-26](#) [T1014-28](#) [T2014-28](#) [10155466-A308ULF](#)
[10155470-A008LF](#) [T3013-24](#) [T3015-28](#) [T1012-24](#) [T2013-26](#) [10155466-A208ULF](#) [T1011-22](#) [10155466-A102ULF](#)
[10155466-A103ULF](#) [10155466-A104ULF](#) [10155466-A105ULF](#) [10155466-A106ULF](#) [10155466-A107ULF](#) [10155470-](#)
[A009LF](#) [10155470-A010LF](#) [10155470-A002LF](#) [10155470-A003LF](#) [10155470-A004LF](#) [10155470-A005LF](#) [10155470-](#)
[A006LF](#) [10155470-A007LF](#) [10155466-A304ULF](#) [10155466-A305ULF](#) [10155466-A306ULF](#) [10155466-A307ULF](#)
[10155466-A309ULF](#) [10155466-A310ULF](#) [10155466-A206ULF](#) [10155466-A207ULF](#) [10155466-A209ULF](#) [10155466-](#)
[A210ULF](#) [10155466-A302ULF](#) [10155466-A303ULF](#) [10155466-A109ULF](#) [10155466-A110ULF](#) [10155466-A202ULF](#)
[10155466-A203ULF](#) [10155466-A204ULF](#) [10155466-A205ULF](#)