






1 | 2 3 | 4 | 5 | 6

view shown without grounding and plastic pin



PC card drilling dimensions (after plating)  
(thickness 1.60 ±0.10 mm)



SHELL	A ± 0.38	B ± 0.12	C ± 0.10	D ± 0.25	E ± 0.07	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE
09	30.81	24.99	18.00	16.21	10.96	D09S82C4GL00	D09S82C6GL00	D09S82C4GL00LF	D09S82C6GL00LF
15	39.14	33.32	26.32	24.54	19.18	D15S82C4GL00	D15S82C6GL00	D15S82C4GL00LF	D15S82C6GL00LF
25	53.03	47.04	40.04	38.25	33.12	D25S82C4GL00	D25S82C6GL00	D25S82C4GL00LF	D25S82C6GL00LF
37	69.32	63.50	56.50	54.71	49.68	D37S82C4GL00	D37S82C6GL00	D37S82C4GL00LF	D37S82C6GL00LF
						Gold flash	0.76 $\mu$ gold	Gold flash	0.76 $\mu$ gold

#### GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code		surface		tolerance		projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			
M	ELX-I-18050	MP	2014/06/23	angles	linear	.0±0.1	D-SUB
						.00±0.1	
						.000±0.1	
				dr	PESSON	1994/03/16	
				engr	MITHUN PAUL	2014/06/23	
				chr	ALIAS BABU	2014/06/23	
				appd	BIJU K PAUL	2014/06/23	
sheet index		revision	M				
sheet		1					



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[D09S82C4GL00LF](#) [D09S82C6GL00LF](#) [D15S82C4GL00LF](#) [D15S82C6GL00LF](#) [D25S82C4GL00LF](#)  
[D25S82C6GL00LF](#) [D37S82C6GL00LF](#) [D09S82C4GL00](#) [D09S82C6GL00](#) [D15S82C4GL00](#) [D15S82C6GL00](#)  
[D25S82C4GL00](#) [D25S82C6GL00](#) [D37S82C6GL00](#) [D37S82C4GL00LF](#)