





| REVISIONS |     |                  |             |     |       |
|-----------|-----|------------------|-------------|-----|-------|
| REV       | ECO | DESCRIPTION      | DATE        | BY  | APPR  |
| B1        | -   | RELEASED DRAWING | JUN-25-2014 | BEN | TOMMY |



- NOTES : (UNLESS OTHERWISE SPECIFIED)**
- MATERIAL :**  
 SHELL : ZINC ALLOY , NICKEL PLATED.  
 JAM NUT : AL ALLOY , NICKEL PLATED.  
 INSERT : THERMOPLASTIC , UL94 V-0/CR.  
 O-RING : NBR.  
 SEAL GASKET : NBR.
  - SPECIFICATIONS :**
    - RATED CURRENT :**
      - 2.1.1 STAMPED CONTACT : 5A (MAX) .
      - 2.1.2 MACHINED CONTACT : 7.5A (MAX) .
    - RATED VOLTAGE : 150V ( AC/DC ) .**
    - OPERATING TEMPERATURE : -40°C ~ +105°C.**
    - DIELECTRIC WITHSTANDING VOLTAGE : LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@1500 VOLTS AC.**
    - INSULATION RESISTANCE : 5000 MEGOHMS MIN.**
    - IP--CLASS : IP67.**
    - MATING CYCLES DURABILITY : 500 CYCLES MIN.**
  - SUITABLE CONTACTS : 20# CONTACTS.**
  - ROHS COMPLIANT.**
  - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.**



| KEY POS | PART NUMBER  |
|---------|--------------|
| N       | RT0W71419SNH |
| W       | RT0W71419SWH |
| X       | RT0W71419SXH |
| Y       | RT0W71419SYH |
| Z       | RT0W71419SZH |

|                                                                                                                                                                                                                                                                      |             |                                                                                                                                                                |                                                      |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------|
| SEE PART NUMBER CHART                                                                                                                                                                                                                                                |             |                                                                                                                                                                |                                                      |
| QUANTITY                                                                                                                                                                                                                                                             | PART NUMBER | DESCRIPTION                                                                                                                                                    | ITEM                                                 |
| MATERIALS LIST                                                                                                                                                                                                                                                       |             |                                                                                                                                                                |                                                      |
| UNLESS OTHERWISE SPECIFIED<br>1) All dimensions are in metric(mm).<br>2) Tolerances are as follows:<br>1 PL DEC ±0.30    Fractions ±1/64<br>2 PL DEC ±0.15    Angles ±1°<br>3 PL DEC ±0.08<br>3) Note reference =                                                    |             | SIGNATURES    DATE<br>DRAWN: BEN    JUN-25-2014<br>CHECKED:<br>ENGINEER:<br>APPROVAL:<br>CUSTOMER:                                                             |                                                      |
| MATERIAL SPECIFICATIONS:<br><br>PROCESS SPECIFICATIONS:<br><br>NEXT ASSY:                                                                                                                                                                                            |             | <br>Sine Systems - www.amphenol-sine.com<br>44724 Morley Drive<br>Clinton Township, MI 48036<br><br>ECO-MATE, RECEPTACLE, JAM NUT,<br>SIZE 14, 19 POS, SOCKET. |                                                      |
| THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. |             | SIZE: B C-<br>SCALE: NONE                                                                                                                                      | DWG NO: RT0W71419S*H<br>REVISION: B1<br>SHEET 1 OF 1 |

ecomate® RM/RSSM/Aquarius™ - Contact Size 20 Options

| Crimp Contacts, Machined |            |       |                  |            |
|--------------------------|------------|-------|------------------|------------|
| Part Number              |            | AWG   | Wire Range (mm²) | Plating    |
| Male                     | Female     |       |                  |            |
| MP20W23F                 | MS20W23F   | 22-20 | 0.34-0.50        | Gold Flash |
| MP20W23G5                | MS20W23G5  | 22-20 | 0.34-0.50        | Gold 5µ"   |
| MP20W23G10               | MS20W23G10 | 22-20 | 0.34-0.50        | Gold 10µ"  |
| MP20W23G15               | MS20W23G15 | 22-20 | 0.34-0.50        | Gold 15µ"  |
| MP20W23G30               | MS20W23G30 | 22-20 | 0.34-0.50        | Gold 30µ"  |
| MP24W23F                 | MS24W23F   | 26-24 | 0.13-0.25        | Gold Flash |
| MP24W23G5                | MS24W23G5  | 26-24 | 0.13-0.25        | Gold 5µ"   |
| MP24W23G10               | MS24W23G10 | 26-24 | 0.13-0.25        | Gold 10µ"  |
| MP24W23G15               | MS24W23G15 | 26-24 | 0.13-0.25        | Gold 15µ"  |
| MP24W23G30               | MS24W23G30 | 26-24 | 0.13-0.25        | Gold 30µ"  |
| MP28W23F                 | MS28W23F   | 30-28 | 0.05-0.08        | Gold Flash |
| MP28W23G5                | MS28W23G5  | 30-28 | 0.05-0.08        | Gold 5µ"   |
| MP28W23G10               | MS28W23G10 | 30-28 | 0.05-0.08        | Gold 10µ"  |
| MP28W23G15               | MS28W23G15 | 30-28 | 0.05-0.08        | Gold 15µ"  |
| MP28W23G30               | MS28W23G30 | 30-28 | 0.05-0.08        | Gold 30µ"  |

| Tooling, Machined |                                              |
|-------------------|----------------------------------------------|
| Part Number       | Description                                  |
| QXRT20            | Contact Extraction Tool, #20 (Ø 1.0) Contact |
| MFY-3959          | Hand Crimp Tool for Machined Contacts        |
| MFY-3960          | Pneumatic Crimp Tool for Machined Contact    |

| Plating Options, All |                                            |
|----------------------|--------------------------------------------|
| Symbol               | Plating                                    |
| T                    | Tin Plated (for Stamped & Formed Contacts) |
| S                    | Silver Plated 5µm (for Machined Contacts)  |
| F                    | Gold Plated                                |
| G5                   | Gold Plated (Thickness 5µ")                |
| G10                  | Gold Plated (Thickness 10µ")               |
| G15                  | Gold Plated (Thickness 15µ")               |
| G30                  | Gold Plated (Thickness 30µ")               |

| Crimp Contacts, Stamped & Formed |           |       |                  |            |
|----------------------------------|-----------|-------|------------------|------------|
| Part Number                      |           | AWG   | Wire Range (mm²) | Plating    |
| Male                             | Female    |       |                  |            |
| SP20W2F                          | SS20W2F   | 22-20 | 0.34-0.50        | Gold Flash |
| SP20W2G5                         | SS20W2G5  | 22-20 | 0.34-0.50        | Gold 5µ"   |
| SP20W2G10                        | SS20W2G10 | 22-20 | 0.34-0.50        | Gold 10µ"  |
| SP20W2G15                        | SS20W2G15 | 22-20 | 0.34-0.50        | Gold 15µ"  |
| SP20W2G30                        | SS20W2G30 | 22-20 | 0.34-0.50        | Gold 30µ"  |
| SP24W2F                          | SS24W2F   | 26-24 | 0.14-0.25        | Gold Flash |
| SP24W2G5                         | SS24W2G5  | 26-24 | 0.14-0.25        | Gold 5µ"   |
| SP24W2G10                        | SS24W2G10 | 26-24 | 0.14-0.25        | Gold 10µ"  |
| SP24W2G15                        | SS24W2G15 | 26-24 | 0.14-0.25        | Gold 15µ"  |
| SP24W2G30                        | SS24W2G30 | 26-24 | 0.14-0.25        | Gold 30µ"  |
| SP28W2F                          | SS28W2F   | 30-28 | 0.05-0.08        | Gold Flash |
| SP28W2G5                         | SS28W2G5  | 30-28 | 0.05-0.08        | Gold 5µ"   |
| SP28W2G10                        | SS28W2G10 | 30-28 | 0.05-0.08        | Gold 10µ"  |
| SP28W2G15                        | SS28W2G15 | 30-28 | 0.05-0.08        | Gold 15µ"  |
| SP28W2G30                        | SS28W2G30 | 30-28 | 0.05-0.08        | Gold 30µ"  |

| Tooling, Stamped & Formed |                                                        |
|---------------------------|--------------------------------------------------------|
| Part Number               | Description                                            |
| QXRT20                    | Contact Extraction Tool, #20 (Ø 1.0) Contact           |
| MFY-3958                  | Hand Tool, Stamped & Formed Contact, Size 20, 20-28AWG |
| MFY-3957                  | Crimp Die for Stamped & Formed Contact                 |

| Misc Tooling, All |                            |
|-------------------|----------------------------|
| Part Number       | Description                |
| CA-4020-59        | Sealing Plug, Size 16 & 20 |

| Standard Quantity Order Options |                   |
|---------------------------------|-------------------|
| Machined                        | Stamped & Formed  |
| Bulk Package, 500 Pieces        | Reel, 3000 Pieces |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RT0W71419SNH](#)