




DIMENSIONS mm (inches)



METHOD OF INSERTION
ON THE PCB = FLAT ROCK



PCB DRILLING



SEE DRAWING C-8609-0000C

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

European Views

PART NUMBER	8609			81		7		8	
PIN OUT									
rows a-b-c	3 48								
rows a-c	4 32								
NUMBER OF CONTACTS									
TERMINATION									
L = 13.10 ±0.20 (0.515)	1 wrap 91								
L = 17.10 ±0.20 (0.673)	2 wraps 92								
L = 3.00 ±0.20 (0.118)	short post 94								
PERFORMANCE CLASS									
DIN 41612 class 3	4								
DIN 41612 class 2	5								
DIN 41612 class 1	6								
TERMINATION TYPE									
TIN LEAD	000E3								
LEAD FREE	E3LF								

www.fciconnect.com	surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm
TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	ROUILLARD	1994/11/14	ANGULAR
Eng	TARON	1994/11/14	LINEAR
Chr	LEGARE	1994/11/14	0.XX ±0.1
Appr	LEGARE	1994/11/14	0.XXX ±0.1
Product family			DIN 8609
Spec ref			-

rev	ecn no	dr	date
D	-	MAS	1999/08/05
E	LS05-004	JTA	2005/02/28
F	LS06-0095	LGO	2006/06/17
G	LS06-0171	HLG	2006/10/27
H	LS07-0051	HLG	2007/02/21
-	-	-	-
-	-	-	-

FCI	title	STRAIGHT FEMALE - STYLE C	dwg no	C-8609-0437	Rev.	H
PRESS FIT		CUSTOMER		sheet 1 of 1		

REV F - 2006-04-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[86094328194758E3LF](#)