


The image contains two technical drawings of PCB drilling details. The left drawing is for 14 & 15 POSN configurations, showing a rectangular board with two circular mounting holes. Dimensions include overall width B, distance E from the left hole to the start of the component holes, distance F from the end of the component holes to the right hole, and distance G between individual component holes. The component holes are arranged in three rows of four. A dimension of 2.54 is shown for the vertical spacing between rows. A note indicates a minimum diameter of 0.90 mm for the component holes. The right drawing is for 26 & 44 POSN configurations, showing a similar layout but with a break symbol (two parallel diagonal lines) in the middle of the component hole array, indicating a longer board. It includes the same dimension labels B, E, F, and G.

FOR 14 & 15 POSN

FOR 26 & 44 POSN

PCB DRILLING DETAILS

[illegible]

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101	
ltr	ecn no	dr	date	tolerances unless	otherwise specified		
D	I06-0074	GVJ	2006-06-08	angles	linear		
E	I09-0202	NG	2009-09-24			.00±0.1	
				0°±1°		.000±.00X	
				dr	GEORGE.V.JOSEPH	2004-10-12	
				engr	NIRMAL.GEORGE	2009-09-24	
				chr	NIRMAL.GEORGE	2009-09-24	
				appd	SUDHIR.VARMA	2009-09-24	
sheet index	revision	D	E				
	sheet	1	1				

Packaging Details
Tape according to EIA-481-B
Anti static Property-
As per EIA-541
Reel ø 330mm
Qty – 75 nos/ reel
Empty Pockets
3 pockets min.and 300mm
extra cover tape at begining
and 5 pockets min. at the end

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ICD26S13E6GV12LF](#)