

NOTES:

1. METALSHELLS: STEEL; min. 320 μ " TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8 μ " HARD GOLD OVER min. 50 μ " NICKEL
4. METAL BRACKET: STEEL; min. 320 μ " TIN over 80 μ " NICKEL
5. THREADED INSERT: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
6. PCB-SNAP: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
PCB-HOLE: ϕ 3.1 \pm 0.1; PCB THICKNESS 1.6mm


⑥ 7. P.C.B. HOLE DRILLINGS ON SHEET 2

8. CONNECTOR IS PART MARKED: PART NO. CONEC ABC
9. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS

10. $\boxed{}$ = CHECK DIMENSION

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	CUSTOMER APPROVAL DATE:	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	NAME:	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	TITLE:	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	COMPANY NAME:	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

		tolerance		 dim. in mm		scale: 2:1	
						material: SEE NOTES	
		2001	date	name		title:	
		drawn	18.09.	E. Mickenbecker		D-SUB HD FEMALE 90° REVERSE	
		appd.	18.09.	A. Mickenbecker		0.314inch 15-62pos.	
		norm				with metal bracket, threaded insert and clip	
		d-old				dwg no: AutoCAD 2000 DIN-A	
						16K1A298A	
						3	
1 x b	Ä 2347	12.10.2005	Lehmen			sh:1/2	
rev.	description	date	name			part no: SEE TABLE	

Directive 2002/95/EC RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[164A05929A](#)