





AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.

No. of pos.	A $^{+0.2}$	B $^{+0.2}$	C	D $_{-0.25}$	PART NO.
9	21.1	39.4	25.00 $^{+0.12}_{-0.13}$	16.46	6STD09SCM99B30X
15	21.1	47.7	33.30 $^{+0.15}_{-0.1}$	24.79	6STD15SCM99B30X
25	21.1	61.4	47.04 $^{+0.13}_{-0.13}$	38.50	6STD25SCM99B30X
37	21.1	77.9	63.50 $^{+0.13}_{-0.13}$	54.96	6STD37SCM99B30X



NOTES:

1. METAL SHELLS: COPPER ALLOY; min. 320 μ " TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30 μ " HARD GOLD OVER min. 50 μ " NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. THREADED INSERT: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
5. COLLAR: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
6. FRAME: ZINC DIECAST; NICKEL PLATED
7. HEXLOCKING SCREW: STAINLESS STEEL
8. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
9. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC
10. _____ = CHECK DIMENSION

Directive 2002/95 EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	CUSTOMER APPROVAL DATE:		
NAME: TITLE:			
COMPANY NAME:			
APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL

				tolerance			scale: 2:1
							material: SEE NOTES
							title: D-SUB FEMALE
							9-37pos. SOLDER CUP
							with threaded insert and hexlocking screw
							dwg no: AutoCAD 2004 DIN-A
							3 sh:1/1
							18K1A424
							part no: SEE TABLE
6	5	4		2	1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[6STD15SCM99B30X](#)