




| REVISIONS |     |                  |             |       |       |
|-----------|-----|------------------|-------------|-------|-------|
| REV       | ECO | DESCRIPTION      | DATE        | BY    | APPR  |
| A1        | —   | RELEASED DRAWING | Mar-24-21   | Blink | Tommy |
| A2        | —   | UPDATE VOLTAGE   | SEP-23-2021 | BLINK | TOMMY |



SEALING PLUGS CAN BE  
PURCHASED SEPARATELY

NOTES : (UNLESS OTHERWISE SPECIFIED)

- MATERIAL :  
SHELL : THERMOPLASTIC , UL94 V-0.  
INSERT : THERMOPLASTIC , UL94 V-0.  
O-RING : NBR OR SILICONE RUBBER.  
SEAL GASKET : NBR OR SILICONE RUBBER.  
END CAP : THERMOPLASTIC , UL94 V-0.  
PLASTIC RING:THERMOPLASTIC , UL94 V-0.  
WIRE SEAL : SILICONE RUBBER.
- SPECIFICATIONS :  
2.1 RATED CURRENT : 45A (MAX).  
2.2 RATED VOLTAGE : 600V ( AC/DC ) .  
2.3 OPERATING TEMPERATURE : SEE CHART.  
2.4 DIELECTRIC WITHSTANDING VOLTAGE : LESS THAN  
2 MILLIAMPS CURRENT LEAKAGE@2000 VOLTS AC.  
2.5 INSULATION RESISTANCE : 5000 MEGOHMS MIN.  
2.6 IP--CLASS : IP67 AND IP69K IN THE MATED CONDITION,  
WIRE SEALS FULLY POPULATED.  
2.7 MATING CYCLES DURABILITY : 500 CYCLES MIN.  
2.8 RoHS COMPLIANT.
- SUITABLE CONTACTS : 8# CONTACTS.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- CONTACT SIZE AND REAR SEAL WIRE RANGE :

| CONTACT SIZE | MIN.<br>INSULATION<br>O.D. | MAX.<br>INSULATION<br>O.D. | SMALL.WIRE<br>RANGE |
|--------------|----------------------------|----------------------------|---------------------|
| 8#           | Ø2.8mm                     | Ø4.1mm                     | 12AWG               |

| KEY | PART NUMBER    |                  |
|-----|----------------|------------------|
|     | -40°C ~ 105°C  | -40°C ~ 125°C    |
| N   | RTS1BS16N4SHEC | RTS1BS16N4SHEC03 |

| QUANTITY                                                                                                                                                                                                                                                                                                | PART NUMBER | DESCRIPTION                                                                                                 | ITEM                                                     |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|
| MATERIALS LIST                                                                                                                                                                                                                                                                                          |             |                                                                                                             |                                                          |
| <b>UNLESS OTHERWISE SPECIFIED</b><br>1) All dimensions are in metric(mm).<br>2) Tolerances are as follows:<br>1 PL DEC ±0.30<br>2 PL DEC ±0.15<br>3 PL DEC ±0.08<br>3) Note reference =                                                                                                                 |             | <b>SIGNATURES</b><br>DRAWN: BLINK<br>CHECKED: ORION<br>ENGINEER: .<br>APPROVAL: TOMMY<br>CUSTOMER:          | <b>DATE</b><br>SEP-23-2021<br>SEP-24-2021<br>SEP-27-2021 |
| <b>MATERIAL SPECIFICATIONS:</b><br>THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. |             | <b>Amphenol</b><br>Sine Systems - www.amphenol-sine.com<br>44724 Morley Drive<br>Clinton Township, MI 48036 |                                                          |
| <b>PROCESS SPECIFICATIONS:</b><br>NEXT ASSY:                                                                                                                                                                                                                                                            |             | EcoMate Aquarius, RECEPTACLE,IN-LINE, SIZE 16, 4 POS,SOCKET,END CAP.                                        | <b>REVISION</b><br>A2                                    |
| <b>SIZE</b><br>B C-                                                                                                                                                                                                                                                                                     |             | <b>DWG NO:</b><br>RTS1BS16*4SHECxx                                                                          | <b>SCALE</b><br>NONE                                     |
| <b>SHEET</b><br>1                                                                                                                                                                                                                                                                                       |             | <b>OF</b><br>1                                                                                              | <b>REVISION</b><br>A2                                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RTS1BS16N4SHEC03](#)