

## 0.50mm Pitch FFC/FPC – F305 Series

### RIGHT ANGLE ZIF FLEX CONNECTOR

F305 series is a 0.50mm pitch right angle ZIF flex connector with front flip mechanism, double contacts and surface mount termination. These connectors feature a height of 2.00mm and are offered in 4 to 60 contacts. This series features a cable thickness of 0.30mm and provides enhanced durability of 30 mating cycles. The connectors come with a robust design and prevent solder and flux wicking. This series is especially suitable for automotive applications.

- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Double contact points provide enhanced contact stability
- Ensures high solderability and high durability



#### TARGET MARKETS



#### FEATURES

- ZIF (Zero Insertion Force) mechanism
- Front flip function
- Double contact points
- Design against solder and flux wicking
- High-temperature thermoplastic housing
- 4 to 60 positions available
- Lead and halogen-free

#### BENEFITS

- Absence of frictional mating wear results in high mating cycle life
- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Ensures enhanced contact stability
- Ensures high solderability
- Wide operating temperature range of  $-40^{\circ}\text{C}$  to  $+105^{\circ}\text{C}$
- Comprehensive range to satisfy different customer requirements
- Meets environmental, health and safety requirements

## TECHNICAL INFORMATION

### MATERIAL

- Housing: LCP, natural color (UL94V-0)
- Actuator: PA9T, black color (UL94V-0)
- Contact: Phosphor bronze, T=0.15mm
- Stator: Brass, T=0.20mm
- Mylar: T=0.10mm, thermostable, yellow color

### MECHANICAL PERFORMANCE

- FFC/FPC Retention Force: 30gf/pin
- Terminal Retention Force: 100gf/terminal min.
- Stator plate Retention Force: 100gf/plate min.
- Durability: 30 mating cycles

### ELECTRICAL PERFORMANCE

- Voltage Rating: 50V AC/DC
- Current Rating: 0.5A
- Contact Resistance: 30MΩ max.
- Insulation Resistance: 500MΩ min.
- Dielectric Withstanding Voltage: No short or breakdown after 500V AC, 2mA, 1min.

### PACKAGING

- Tape & Reel

### APPROVALS AND CERTIFICATIONS

- UL file number E106764
- RoHS compliant

### SPECIFICATION

- Aorora Product Specification: IS.EQC.083

### ENVIRONMENTAL

- Operating Temperature Range: -40°C to +105°C

### TARGET MARKETS/APPLICATIONS



Car Multimedia  
Car Navigation  
Dashboard  
PND



Base Station  
Power  
Switches



Notebook  
Tablets  
Wearables  
Gaming  
DSC  
LCD & PDP TV



Router  
Server  
ODD  
HDD




Sensing element  
Monitoring camera  
Human Machine Interface  
Industrial PC  
Robotics



Ultrasonic  
Patient Monitor  
MRI  
CT  
Infusion Pump

## PART NUMBER SELECTOR



AORORAF305109EA4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[F305-1A7H1-11006-E100](#) [F305-1A7H1-11010-E100](#) [F305-1A7H1-11015-E100](#) [F305-1A7H1-11040-E100](#) [F305-1A7H1-11060-E100](#) [F305-1A7H1-21021-E100](#) [F305-1A7H1-21022-E100](#) [F305-1A7H1-21024-E100](#) [F305-1A7H1-21060-E100](#) [F3051A7H111006E200](#) [F3051A7H111010E200](#) [F3051A7H111014E200](#) [F3051A7H111015E200](#) [F3051A7H111021E200](#) [F3051A7H111022E200](#) [F3051A7H111024E200](#) [F3051A7H111040E200](#) [F3051A7H111060E200](#) [F3051B7H121070E100](#)