

PRODUCT NUMBER
10119333-YXX-XXLF

PLATING
1=0.76µm GXT/GOLD ON CONTACT
2µm TIN MIN ON TAILS
4=2µm TIN MIN FULL PLATED

RoHS COMPATIBLE
NOTE 4


TOTAL NUMBER OF
POSITIONS :
02 TO 25 POS

PACKAGING, NOTE 3





STYLE	DIM"A"±0.2
01	5.84
02	8.08
03	10.67
04	3.00

NOTES:

- 1- MATERIAL:
 - BODY: HIGH TEMPERATURE THERMOPLASTIC
UL94V-0 COLOR BLACK
 - PIN : COPPER ALLOY
- 2 - TO DETERMINATE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS x 2.54=20.32
- 3 - PACKAGING:
 - A = TAPE & REEL PACKAGING WITH PICK -UP CAP
AS PER GS-14-2357
 - K= T&R PACKAGING WITHOUT PICK UP CAP,
AS PER GS-14-2357
 - = POLYBAGS
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS :
 - a - PLATING :
"LF" MEANS THE PRODUCT IS LEAD FREE
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATED
 - b - MANUFACTURING PROCESS COMPATIBILITY :
THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN
 - c - LABELLING :
MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT :SEE GS-47-0004
- 5 - PRODUCT SPECIFICATIONS AS PER BUS-12-114
EXCEPT PIN RETENTION FORCE 5N MIN.



SCALE 3:1



spec ref				dr	Aymeric Soudy	2014/02/21	projection		MM		size	A3	scale	5:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Pro Engineer 1	2014/04/23					ecn no	-			
				chr	Laurent Mulin	2014/04/23									
ISO 406				appr	J M Maire	2014/04/23	product family		BSTIK	rel level				Released	
surface		linear	0.X	±0.3		title			2.54mm UNSH HEADER HORIZ			dwg no	10119333		rev
			0.XX	±0.13											
			0.XXX	±0.050											
ISO 1302	angular	0°	±2°	www.fci.com	cat. no.		-	Product - Customer Drw				sheet 1 of 1		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10119333-402A10LF](#) [10119333-401A02LF](#) [10119333-101A02LF](#) [10119333-401A04LF](#)