


CFP4

Amphenol ICC's CFP4 series offers a 56 position, 0.6mm pitch connector and is used in multi-hundred Gb/s systems. It is comprised of insert molding assemblies for top side contacts and press-fit cage assemblies. Rated for 25Gb/s per channel with resonance dampening for improved signal integrity, CFP4 has up to 60% lower power consumption versus CFP. The CFP4 series includes a plug connector on the mating interface to improve accuracy and aid in delivering high speed performance. CFP4 has the ability to be a customized solution with an optional riding heat sink that ensures proper thermal dissipation. It is also compliant with IEEE and ITU-T applications.



TARGET MARKETS



TECHNICAL INFORMATION

MATERIAL

- Housing: Black color, Glass reinforced, Lead Free Solder Reflow Process Compatible Thermo Plastic
- Contacts Base Material: Phosphor Bronze
- Plating Solder Tails: Matte tin
- Plating Mating Area: Gold
- Resonance Dampening Feature: Conductive Polymer

MECHANICAL PERFORMANCE

- Durability: 200 mating cycles
- Mating Force: 60 N max.
- Contact Normal Force: 40 grams
- PCB Thickness (Cage): 3.00 mm (0.118 in.)
- Unmating Force (Cage): 50 N
- Insertion Force to PCB (Cage) : 2 port – 2000N max.

ELECTRICAL PERFORMANCE

- Operating Voltage: 3.3 V DC per contact
- Operating Current: 1.87 A per contact

ENVIRONMENTAL

- Operating and (Storage) Temperature: -40°C to +85°C
- RoHS & Halogen-Free

TOOLING INFORMATION

- Configurations: 1X1, 1X2, 1X4

TARGET MARKETS/APPLICATIONS



Metro Area Networks



Carrier Networks and Data Centers
Large Data Center Campus Connectivity

PART NUMBER SELECTOR

CFP4 Host Connector

U99

C

056

X

0

0

T

Style

C

CFP4 Connector

Number of Positions

056

56 Positions

Contact Plating

2

30 μ" (0.76 μm) Gold Plating on Mating Area; Matte Tin Plating on Termination

3

15 μ" (0.38 μm) Gold Plating on Mating Area; Matte Tin Plating on Termination

Packaging

T

Tape & Reel

Option 2

0

Standard

Option 1

0

Standard

CFP4 Cage

U98

C

X

X

X

1

X

X

1

Style

C

CFP4 Cage

Number of Port in row

1

1X1

2

1X2

4

1X4

Heat Sink Options

1

No Heat Sink & No Clip Shipped

2

Fin, Side to Side, Aluminum Alloy, Black Anodize Coating - 14mm

6

Fin, Side to Side, Aluminum Alloy, Black Anodize Coating - 11mm

B

Post, Aluminum Alloy, Black Anodized - 11mm

M

Fin, Front to Back, Aluminum Alloy, Black Anodize Coating - 14mm

Packaging

1

Tray

Connector Cover

B

Without Connector Cover

C

With Connector Cover

Optional Dust Cover

0

Without Dust Cover

D

With Dust Cover (Shipped Loose)

Plating

1

Nickel

Insulating Tape Option

1

Standard (No Insulating Tape)

2

With Insulating Tape on Bottom Cage

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[U99-C056-200T](#) [U98-C121-10C1](#) [U98-C421-10C1](#) [U98-C221-10C1](#) [U98C11110B1](#) [U98C11110C1](#) [U98C1M110C1](#)