


SIGN	DATE	DESCRIPTION	APPROVER
△	01/20'07	The Soldering temperature from 245° to 250°	Aaron
△	2010.08.12	The design is changed	Chen Bo
△	2012.07.18	The tolerance are added	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

## Material

- Terminal lever: Thermoplastic (UL94 V-0) Orange RAL2011/P
- Terminal housing: Thermoplastic (UL94 V-0)
- Terminal cover: Thermoplastic (UL94V-0)
- Solder Pin : Brass Tin plated
- Wire guard: Stainless steel

## Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm<sup>2</sup>
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec △
- Safety Approval: 
- Critical dimension: △

HA xx 01 x 0 xxxx G

02 2 Poles  
03 3 Poles  
...  
24 24 Poles

Body color

2 Red  
3 Orange  
5 Green(RAL6018/T)  
8 Grey(RAL7004/P)

RoHS compliant  
(lead<4%)  
In copper Alloy

0000: "@" Logo (Standard)  
000A: "ANYTEK" Mark  
Any special item by  
customer request.  
please contact sales  
department.


△ N = Number of poles  
Dim L=(N×5.08)+2.54  
Dim P=(N-1)×5.08

Poles	Dim L	Dim P
2-6p	±0.20	
7-12p	±0.25	
13-24p	±0.40	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HA-5.08mm 180° series					
PART NO.		HAxx01x0xxxxG		DWG NO.	8HA0102		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Runner 2012.07.18	Chen Bo 2010.08.12		Tolerance		
					X.	±0.50	
					X.X	±0.30	
					X.XX	±0.10	
				SHEET: 01/01	REV.: G	X°	±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>HA0701500000G</u></a>	<a href="#"><u>HA1701500000G</u></a>	<a href="#"><u>HA0301500000G</u></a>	<a href="#"><u>HA1201500000G</u></a>	<a href="#"><u>HA2201500000G</u></a>	<a href="#"><u>HA1101500000G</u></a>
<a href="#"><u>HA1401500000G</u></a>	<a href="#"><u>HA0901500000G</u></a>	<a href="#"><u>HA0601500000G</u></a>	<a href="#"><u>HA0801500000G</u></a>	<a href="#"><u>HA1001500000G</u></a>	<a href="#"><u>HA0401500000G</u></a>
<a href="#"><u>HA2101500000G</u></a>	<a href="#"><u>HA1501500000G</u></a>	<a href="#"><u>HA2301500000G</u></a>	<a href="#"><u>HA1301500000G</u></a>	<a href="#"><u>HA2401500000G</u></a>	<a href="#"><u>HA0501500000G</u></a>
<a href="#"><u>HA1801500000G</u></a>	<a href="#"><u>HA1901500000G</u></a>	<a href="#"><u>HA2001500000G</u></a>	<a href="#"><u>HA1601500000G</u></a>	<a href="#"><u>HA0201500000G</u></a>	