

HD

D-Sub connectors - Stamped and Formed Contacts

RIGHT ANGLE HIGH DENSITY CONNECTORS

Specifications


- Connector interfaces according to: MIL C24308
- UL File: E232356

Materials and Platings	
Shells	Steel, tin over nickel plating
Insulator	Glass-filled thermoplastic, UL 94V-0
Contacts	Brass, selected gold in mating area; 2.54µm (100µ") min. tin on termination area over 1.27µm (50µ") min. nickel
Rear insert	Brass, 2.54µm (100µ") min. nickel plated
Boardlock	Brass, 2.54µm (100µ") min. nickel plated
Screwlock	Brass, 2.54µm (100µ") min. nickel plated

Electrical Data	
Current rating	3A
Voltage rating	250V AC/ rms 50Hz
Withstanding voltage	1000V AC/rms 50Hz for one minute
Insulation resistance	5000MΩ at 500V DC
Contact resistance	25mΩ max

Climatic Data	
Operating temperature	-55°C to +105°C
Salt spray	24 hours

Mechanical Data		
Single contact insertion force	0.34kg (0.75lb) max.	
Single contact withdrawal force	0.02kg (0.044lb) min.	
Mating and unmating force		
Unit: kg (lb)		
No. of Cts	Mate (max)	Unmate (min)
15	3.81 (8.42)	0.52 (1.14)
26	5.95 (13.16)	1.05 (2.32)
44	9.26 (20.46)	1.37 (3.02)
62	13.48 (29.78)	1.76 (3.88)
Standard plating thickness		
• Gold flash		
• 0.38µm (15µ") Gold		
• 0.76 µm (30µ") Gold		



DESCRIPTION

Amphenol's high density D-Sub connectors complement Amphenol's extensive D-Sub connector line. This line offers many superior features, high performance level and low installation cost.

The decreased contact spacing accommodates greater signal density in comparison to conventional D-Sub connectors.

*Economical
right angle PCB
connectors*

APPLICATIONS

- Industrial
- Telecom
- Any industry standard I / O connections




Amphenol


HD / E19

Shell size dimensions

Pin




Socket




Nb OF CONTACTS	DIMENSIONS mm (inch)				
	A	B	C	C'	D
15	30.84 (1.214)	24.99 (.984)	16.92 (.661)	16.26 (.640)	2.29 (.090)
26	39.24 (1.545)	33.32 (1.312)	25.25 (.994)	24.56 (.967)	2.29 (.090)
44	53.04 (2.088)	47.04 (1.852)	38.96 (1.534)	38.30 (1.508)	2.29 (.090)
62	69.34 (2.730)	63.50 (2.500)	55.42 (2.182)	54.76 (2.156)	2.41 (.095)

P.C.B. Layout




PCB layout for Socket connector, top view

Panel mounting option



How to order



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[L717HDA26PD1CH3FC309](#) [L717HDA26PD1CH3RC309](#) [L717HDA26PD1CH4FC309](#) [L717HDA26PD1CH4RC309](#)
[L717HDB44PD1CH3FC309](#) [L717HDB44PD1CH3RC309](#) [L717HDB44PD1CH4FC309](#) [L717HDB44PD1CH4RC309](#)
[L717HDC62PD1CH3FC309](#) [L717HDC62PD1CH3RC309](#) [L717HDC62PD1CH4FC309](#) [L717HDC62PD1CH4RC309](#)
[L717HDE15PD1CH3FC309](#) [L717HDE15PD1CH3RC309](#) [L717HDE15PD1CH4FC309](#) [L717HDE15PD1CH4RC309](#)
[L77HDC62SD1CH3RC309](#) [L77HDB44SD1CH4FC309](#) [L77HDC62SD1CH3FC309](#) [L77HDB44SD1CHC309](#)
[L77HDB44SD1CH3RC309](#) [L77HDA26SD1CH3FC309](#) [L77HDC62SD1CH4FC309](#) [L77HDE15SD1CH3RC309](#)
[L77HDE15SD1CH4RC309](#) [L77HDA26SD1CH3RC309](#) [L77HDB44SD1CH4RC309](#) [L77HDC62SD1CH4RC309](#)
[L77HDE15SD1CH4FC309](#) [L77HDA26SD1CH4FC309](#) [L77HDB44SD1CH3FC309](#) [L77HDA26SD1CH4RC309](#)
[L77HDE15SD1CH3FC309](#) [L77HDE15SD1CO4RC309](#) [L717HDA26PD1CHC309](#) [L717HDE15PD1CHC309](#)
[L717HDE15PD1CO4RC309](#)