




SECTION B-B



SECTION C-C

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPROVED
A1	-	RELEASED DRAWING	May-15-2019	Flan	Tommy
A2	-	UPDATE DRAWING	Aug-9-2019	Flan	Tommy
A3	-	UPDATE DRAWING	Jun-29-2020	Ronald	Tommy

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:
 - 1.1. CONTACT: COPPER ALLOY.
2. SPECIFICATIONS:
 - 2.1 CURRENT RATING: 5A MAX.
 - 2.2 TERMINATION TYPE: CRIMPING.
 - 2.3 WIRE RANGE: 20~22AWG.
 - 2.4 WIRE INSULATION DIA (MAX): Ø1.8mm.
3. RoHS COMPLIANT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

P/N	CONTACT PLATING (* MATING AREA ONLY)
SC000572T	TIN PLATING OVER NICKEL.
SC000572N	NICKEL PLATING OVER COPPER.
SC000572F	GOLD FLASH PLATING OVER NICKEL.
SC000572G5	* 5μ"GOLD PLATING OVER NICKEL.
SC000572G10	* 10μ"GOLD PLATING OVER NICKEL.
SC000572G15	* 15μ"GOLD PLATING OVER NICKEL.
SC000572G30	* 30μ"GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION			ITEM NO.
MATERIALS LIST					
UNLESS OTHERWISE SPECIFIED:		SIGNATURES	DATE	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 DURALOK ATV, SOCKET CONTACT STAMPED, 20-2ZAWG B SIZE TYPE DWG NO: C- SC000572x REV: A SCALE: NONE SHEET 1 OF 1	
1) All dimensions are in metric(mm).		DRAWN: Ronald	Jun-29-2020		
2) Tolerances are as follows:		CHECKED: Fian	Jun-30-2020		
1 PL DEC ±0.30 1 Fractions ±1/64		ENGINEER:			
2 PL DEC ±0.15		APPROVAL: Tommy	Jun-30-2020		
3) Note reference =		CUSTOMER:			
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION, NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
PROCESS SPECIFICATIONS:					
NEXT ASSY:					

TITLE: DURALOK ATV, SOCKET CONTACT, STAMPED, 20-22AWG

DWG NO	
--------	--

SC000572x

REV: A3

SH:

OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SC000572G10](#)