





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	DEC-12-2019	BLINK	TOMMY
A2	-	UPDATE DRAWING	MAR-18-2020	BLINK	TOMMY



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

1.1 CONTACT BODY: COPPER ALLOY,SILVER PLATED.

2. SPECIFICATIONS:

2.1 CURRENT RATING: 32A(MAX).

2.2 TERMINATION TYPE: CRIMPING.

2.3 WIRE RANGE: 10~12AWG.

3. RoHS COMPLIANT.

4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ± 0.30 Fractions $\pm 1/64$ 2 PL DEC ± 0.15 Angles $\pm 1^\circ$ 3 PL DEC ± 0.08 3) Note reference =		SIGNATURES DRAWN: BLINK CHECKED: ORION ENGINEER: APPROVAL: TOMMY CUSTOMER: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
DATE: MAR-18-2020 MAR-20-2020 MAR-23-2020		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
MATERIAL SPECIFICATIONS:		2.4MM, CONTACT, PIN WIRE RANGE 10-12 AWG	
PROCESS SPECIFICATIONS:		SIZE: B TYPE: C- SCALE: NONE	REVISION: A2
NEXT ASSY:		DWG NO: SC000611 SHEET 1 OF 1	

TITLE: 2.4MM CONTACT PIN
DWG NO: SC000611
REV: A2
SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SC000611](#)