


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	05/04/15	



Amphenol
P/N: SF-10GSFPPLCL-000
850nm MM 10G 300m

APX20150000001 Made in Taiwan
CLASS 1 21 CFR1040.10



SERIAL NO. BREAKDOWN:





APXWWYYXXXSSSS

SERIAL NUMBER (EX: 0001, 0002, ETC.)

LAST 3 DIGITS OF ACD P/N

MFG YEAR

MFG WEEK



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS		ANGLES
.X	±.X	± X°
.XX	±.XX	
.XXX	±.XXX	

THIRD ANGLE PROJECTION



EAR NO.

APPROVALS

DATE

DRAWN

LF

05/04/15

CHECKED

BA

05/04/15

RESP ENG

MFG ENG

Amphenol Cables on Demand

20 VALLEY ST. ENDICOTT, NY 13760

SFP+ MM OPTICAL MODULE

SIZE
A

DWG. NO.

SF-10GSFPPLCL-000

REV.
A0

NOTES: UNLESS OTHERWISE SPECIFIED


CAD FILE:

SCALE


SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	05/04/15	



PIN	Logic	Symbol	Name / Description	Note
1		VeeT	Module Transmitter Ground	1
2	LVTTL-O	TX_Fault	Module Transmitter Fault	
3	LVTTL-I	TX_Dis	Transmtiter Disable; Turns off transmitter laser output	
4	LVTTL-I/O	SDA	2-Wire SerialInterface Data Line	2
5	LVTTL-I	SCL	2-Wire SerialInterface Clock	2
6		MOD_DEF0	Module Definition, Grounded in the module	
7	LVTTL-I	RS0	Not used	
8	LVTTL-O	RX_LOS	Receiver Loss of Signal Indication Active High	
9	LVTTL-I	RS1	Not used	
10		VeeR	Module Receiver Ground	1
11		VeeR	Module Receiver Ground	1
12	CML-O	RD-	Receiver Inverted Data Output	
13	CML-O	RD+	Receiver Data Output	
14		VeeR	Module Receiver Ground	1
15		VccR	Module Receiver 3.3 V Supply	
16		VccT	Module Receiver 3.3 V Supply	
17		VeeT	Module Transmitter Ground	1
18	CML-I	TD+	Transmtiter Non-Inverted Data Input	
19	CML-I	TD-	Transmitter Inverted Data Input	
20		VeeT	Module Transmitter Ground	1



NOTES: UNLESS OTHERWISE SPECIFIED



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMALS .X ±.X ANGLES .XX ±.XX ± X° .XXX ±.XXX	EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760		
	APPROVALS	DATE			
THIRD ANGLE PROJECTION 	DRAWN	LF	05/04/15	SFP+ MM OPTICAL MODULE	
	CHECKED	BA	05/04/15		
	RESP ENG				
		MFG ENG		SIZE A	DWG. NO. SF-10GSFPPLCL-000
CAD FILE:				REV. A0	
			SCALE	SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SF-10GSFPPLCL-000](#)