

Modular Jack – RJE58 Series

CAT5e, RIGHT ANGLE, SINGLE PORT CONNECTOR WITH AVAILABLE LEDs

The RJE58 single port series of Modular Jacks meet CAT5e performance per EIA-568-C.2 standards. It supports 1G and 2.5G Ethernet data rates and transmissions frequencies up to 100MHz. Shielding is available for increased EMI performance and LEDs are incorporated for link activity and network speed verification. The connectors are highly durable with 750 mating & unmating cycles. They also support an operating temperature of -55°C to +85°C, making them suitable for a wide range of environmental conditions.

- Supports 1G and 2.5G Ethernet Protocols
- Meets CAT5e performance on its own without outside assistance
- Same size and footprint as the RJE59 and RJE60 series
- Multiple shield and LED options available
- RoHS compliant

FEATURES

- Variety of LED options
- Standard size
- Accommodates industry standard plugs
- Reflow compatible
- Available with and without shielding
- Meets CAT5e performance per EIA-568-C.2.



TARGET MARKETS



BENEFITS

- Customers can opt for the LED color of their choice
- Optimizes the PCB space
- Can mate successfully with all types of standard plugs
- Single process for soldering to PCB, saving time and money
- Accommodates a wide range of EMI needs
- Supports 1G and 2.5G Ethernet

TECHNICAL INFORMATION

MATERIAL

- Insulator: High temperature engineering thermoplastic; Complies with UL94V-0, Black
- Contacts: Phosphor bronze hard temper with gold thickness options (6u", 15u", 30u", 50u") over 50u" min. nickel on contact mating area. 100u" min. matte tin plating on soldering tail
- Shield: Copper alloy, nickel plated with tin dipped tail or stainless steel with tin dipped tail
- LED: Pure tin plating on LED tails

ELECTRICAL PERFORMANCE

- Contact Resistance: 20 mΩ max.
- Insulation Resistance: 500 MΩ min. at 500V DC for 2 minutes max.
- Current Rating: 1.5 Amps
- Voltage Rating: 125V AC
- Dielectric Withstanding Voltage: 1000V AC, 60 Hz., 1 minute
- LED Forward DC Current: 20mA typical
- LED Forward Voltage: 1.9 Volts max. @ 2 mA (for single colors), 2.6 Volts max. @ 20 mA (for bicolors)
- LED Reverse Voltage: 5 Volts min.
- LED Light Intensity: 0.4 to 1.5 mcd @ 2 mA (for single colors), 0.5 mcd min. @ 2 mA (for bicolors)
- LED Wave Length: Yellow – 587 +/- 7 nm measured @ 20 mA, Green – 565 +/- 7 nm measured @ 20 mA, Red – 625 +/- 5 nm measured @ 20 mA

MECHANICAL PERFORMANCE

- Insertion Force: 5 lbs max.
- Pull Retention Force: 20 lbs min.
- Durability: 750 mating and unmating cycles

SPECIFICATION

- Amphenol Product Specification: S6078C

APPROVALS AND CERTIFICATIONS

- RoHS
- REACH
- UL

ENVIRONMENTAL

- Operating Temperature: -55°C to +85°C
- Recommended Soldering Temperature: Wave soldering peaked at 260°C for 5 seconds max.

PACKAGING

- Available in tray and tape and reel packaging

TARGET MARKETS/APPLICATIONS



5G Wireless
Telephones
Modems
Fax Machines
Copiers/printers



Security Systems
Set Top Boxes
Video Game Systems
PCs
Laptops



Storage
Servers
Routers
Switches
Hubs



Uninterruptible Power Supply (UPS)
ATMs
Vending Machines
POS Terminals
Industrial IoT Platforms



Analysis equipment
Mass Spectrometers

PART NUMBERS

Product	Description	Part Numbers
RJE58 Modular Jack Series	Shield with top and side EMI tabs, no LEDs	RJE58-188-5401
RJE58 Modular Jack Series	Shield with top and side EMI tabs, with LEDs	RJE58-188-5441
RJE58 Modular Jack Series	Shield with top and side EMI tabs, with LEDs	RJE58-188-5411
RJE58 Modular Jack Series	Shield with no EMI tabs, no LEDs	RJE58-188-6401
RJE58 Modular Jack Series	Shield with no EMI tabs, with LEDs	RJE58-188-6441
RJE58 Modular Jack Series	Shield with no EMI tabs, with LEDs	RJE58-188-6411
RJE58 Modular Jack Series	Shield with no EMI tabs, with LEDs	RJE58-188-64A1
RJE58 Modular Jack Series	Shield with top and side EMI tabs, with LEDs	RJE58-188-5411
RJE58 Modular Jack Series	Shield with top EMI tabs, no LEDs	RJE58-188-3401
RJE58 Modular Jack Series	Shield with top EMI tabs, with LEDs	RJE58-188-3411
RJE58 Modular Jack Series	Shield with top EMI tabs, with LEDs	RJE58-188-3441
RJE58 Modular Jack Series	Shield with top EMI tabs, with LEDs	RJE58-188-34A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

RJE581885421	RJE581885431	RJE581885461	RJE581885471	RJE581885481	RJE581885491	RJE5818854P1
RJE5818854R1	RJE5818854T1	RJE5818854V1	RJE5818854H1	RJE5818854J1	RJE5818854K1	RJE5818854L1
RJE5818854M1	RJE5818854N1	RJE5818854B1	RJE5818854C1	RJE5818854D1	RJE5818854E1	RJE5818854F1
RJE5818854G1	RJE581883411	RJE581883421	RJE581883431	RJE581883441	RJE581883451	RJE581883461
RJE5818834T1	RJE5818834V1	RJE5818834K1	RJE5818834L1	RJE5818834M1	RJE5818834N1	RJE5818834P1
RJE5818834R1	RJE5818834D1	RJE5818834E1	RJE5818834F1	RJE5818834G1	RJE5818834H1	RJE5818834J1
RJE581883471	RJE581883481	RJE581883491	RJE5818834A1	RJE5818834B1	RJE5818834C1	RJE581883401
RJE5818864P1	RJE5818864R1	RJE5818864T1	RJE5818864V1	RJE5818864H1	RJE5818864J1	RJE5818864K1
RJE5818864L1	RJE5818864M1	RJE5818864N1	RJE5818864B1	RJE5818864C1	RJE5818864D1	RJE5818864E1
RJE5818864F1	RJE5818864G1	RJE581886431	RJE581886461	RJE581886471	RJE581886481	RJE581886491
RJE5818864A1	RJE581883406N	RJE581883416N	RJE581883426N	RJE581883436N	RJE581883446N	
RJE5818864P6N	RJE5818864R6N	RJE5818864T6N	RJE5818864V6N	RJE5818864H6N	RJE5818864J6N	
RJE5818864K6N	RJE5818864L6N	RJE5818864M6N	RJE5818864N6N	RJE5818864B6N	RJE5818864C6N	
RJE5818864D6N	RJE5818864E6N	RJE5818864F6N	RJE5818864G6N	RJE581886456N	RJE581886466N	
RJE581886476N	RJE581886486N	RJE581886496N	RJE5818864A6N	RJE5818854V6N	RJE581886406N	