

TABLE I - PART NUMBER SCHEME		
PART NO.	CONTACTS SUPPLIED	PART MARKING
SJS503190P	NONE	SJS503190P
SJS503191P	(3) M39029/58-360	

"SJS503190P"
INK MARKING
TEXT HEIGHT: .03
COLOR: CONTRASTING


LINEAR SPACING
.100 ON ϕ .116
REF

SJS503190P

4X R.150





GROMMET MARKING
TEXT HEIGHT: .040
COLOR: CONTRASTING

REV	ECN	APP'D
-	7898	MD 3/13/17




O-RING NOT SHOWN FOR
VERTICAL MOUNTING
DIMENSION CLARIFICATION

INK MARKING
TEXT HEIGHT: .03
COLOR: BLACK




- NOTES:
- MATERIALS:
HOUSING: POLYETHERIMIDE, COLOR GREEN.
CONTACT RETAINER: STAINLESS STEEL
JAM NUT: ALUMINIUM ALLOY
O-RING: CONDUCTIVE SILICONE RUBBER
GROMMET: SILICONE RUBBER PER A-A-59588, COLOR RED.
 - FINISH:
HOUSING: NICKEL, 200 MICROINCHES MINIMUM
OVER COPPER, 120 MICROINCHES MINIMUM
 - PARTS ACCEPTS PIN CONTACTS PER TABLE I.
 - PART MATES WITH SJS830210P/211P
 - EST. WEIGHT: 1.7 GRAMS
 - SUPPLIED WITH DUST CAP.

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING		TITLE JAM NUT REAR MOUNT RECEPTACLE SHELL SIZE 5 SJS PEGASUS 3 POS SIZE 22		
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		ENGR ANDREW.WANG Feb-28-15	CHKD <i>Wilton Jann</i> 3/13/17	SIZE B	DWG NO. SJS503190P	REV -
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		APPD <i>Mr. [Signature]</i> 3/13/17		CODE: 58982	SCALE: 3:1	SHEET 1 OF 2



MOUNTING INSTRUCTIONS

SCALE 5:1



MOUNTING PANEL CUTOUT

SCALE 5:1

SIZE	DWG NO.	REV
B	SJS503190P	-
CODE: 58982	SCALE: 3:1	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SJS503190p](#)