




Dimension

DIM A	N×5.08
DIM B	(N-1)×5.08

N=Number of poles

POLES	TOL
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40



P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	8/07'06	Added FIMKO standard	梁仁松
△	01/18'07	Soldering temperature changed from 245° to 250°	Tason
△	01/18'07	Part NO is Changed	Tason

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin :Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

△ Electrical cULus/FIMKO

- Voltage rating: 300VAC/300VAC
- Current rating: 16A/17.5A
- Wire range: 0.5 ~ 1.5mm²
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In./0.5Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus FI

△ VI xx 21 x 0 xxxx G

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

0 Black
5 Green
6 Blue
8 Grey

0000:"@Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

Pb < 40,000ppm
(RoHS)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VI 5.08 SERIES 90° wire inlet								
PART NO.	VIxx21x0xxxxG			DWG NO.	8VI0102				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		熊海燕 2007.01.18	熊海燕 2007.01.18		UNIT: mm		X.	±0.50	
					SCALE: NONE		X.X	±0.30	
					SHEET: 01/01		X.XX	±0.10	
					REV: F		X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VI0221500000G</u>	<u>VI0321500000G</u>	<u>VI0421500000G</u>	<u>VI0521500000G</u>	<u>VI0621500000G</u>	<u>VI0721500000G</u>
<u>VI0821500000G</u>	<u>VI0921500000G</u>	<u>VI1021500000G</u>	<u>VI1121500000G</u>	<u>VI1221500000G</u>	<u>VI1321500000G</u>
<u>VI1421500000G</u>	<u>VI1521500000G</u>	<u>VI1621500000G</u>	<u>VI1721500000G</u>	<u>VI1821500000G</u>	<u>VI1921500000G</u>
<u>VI2021500000G</u>	<u>VI2121500000G</u>	<u>VI2221500000G</u>	<u>VI2321500000G</u>	<u>VI2421500000G</u>	