

SIGN	DATE	DESCRIPTION	APPROVER
△	12/12'07	The screw changed from M4 to M4.5	Aaron
△	4/01'09	Current, wire range, operating temperature are changed	Jody
△	11/20'09	The longest poles changed from 24P to 12P	Aaron
△	11/20'09	Wire guard solder pin is changed from Brass to Copper	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Steel stamping , Zinc plated
- △ ● Item 3 Wire guard solder pin : Copper , Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus IEC

- Voltage rating : 300V 250V
- △ ● Current rating : 65A 57A
- Wire range :
- △ ● Solid wire (AWG) : 6-20 / 0.5-16mm²
- △ ● Stranded wire (AWG) :6-20 / 0.5-10mm²
- Torque (LB-In.) : 19Lb-In / 1.2 N.m
- △ ● Screw : M4.5
- Wire strip length : 10~11mm
- Withstanding voltage : 1.6KV / 4KV
- △ ● Operating temperature : -40°C+115°C
- Soldering temperature : 250°C+10°C/5 Sec
- Safety Approval : cULus

VP xx 65 x 5 xxxx G


02 2 CONTACTS	0 Black	0000:"@Logo (Standard)	RoHS
03 3 CONTACTS	5 Green	000A:"ANYTEK"Logo	Pb<40,000ppm
... ..	(RAL 6018/T)	Any special item by	
△ 12 12 CONTACTS	6 Blue	customer request,	
	8 Grey	please contact sales	
	(RAL 7035/D)	department.	

Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76	121.92
Dim B	10.16	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76
TOL	±0.15			±0.25			±0.35				

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VP 10.16 Series 2P~12P (double contact)						
PART NO.		VPxx65x5xxxxG			DWG NO.		8VP0004	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Aaron 2009.11.20	JODY 2009.4.1			UNIT: mm	X. ±0.50
					SHEET: 01/01		SCALE: NONE	X.X ±0.30
					REV.: I		X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VP0265850000G](#) [VP0365850000G](#) [VP0465850000G](#) [VP0565850000G](#) [VP0665850000G](#) [VP0765850000G](#)
[VP0865850000G](#) [VP0965850000G](#) [VP1065850000G](#) [VP1165850000G](#) [VP1265850000G](#)