




REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
B1	-	RELEASED DRAWING	JAN-18-2014	ARROW TOMMY
B2	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



CONTACT ORIENTATION ON ROLL



- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. MATERIAL:
- 1.1. CONTACT BODY: COPPER ALLOY.
- 1.2. OUTER SPRING: STAINLESS STEEL.
2. SPECIFICATIONS:
- 2.1 CURRENT RATING: 5A MAX.
- 2.2 TERMINATION TYPE: CRIMPING.
- 2.3 WIRE RANGE: 22~20AWG.
- 2.4 WIRE INSULATION DIA(MAX): Ø2.6mm.
3. ROHS COMPLIANT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
5. AVAILABLE TOOLS:
- 5.1 HAND CRIMPER: MFX-3958 ^{B2}
- 5.2 CRIMP APPLICATOR: MFX-3957.
- 5.3 EXTRACTION TOOL: QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS20W1T	TIN PLATING OVER NICKEL.
SS20W1F	GOLD FLASH PLATING OVER NICKEL.
SS20W1G10	10µ" GOLD PLATING OVER NICKEL.
SS20W1G15	15µ" GOLD PLATING OVER NICKEL.
SS20W1G30	30µ" GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	
1) All dimensions are in millimeters.		DRAWN:	DATE
2) Tolerances are as follows:		Rm	Nov-8-19
1 Pk. DEC 40.00		CHECKED:	
3 Pk. DEC 20.00		Mth	Nov-8-19
3) Note reference = 		ENGINEER:	
MATERIAL SPECIFICATIONS		APPROVAL:	
		Tommy	Nov-8-19
CUSTOMER:			
THIS DRAWING IS SUPPLIED FOR YOUR INFORMATION ONLY. IT DOES NOT CONSTITUTE A CONTRACT. SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF AMPHENOL. NO PARTS OR COMPONENTS OF REPRODUCTION ARE TO BE USED. ALL DIMENSIONS ARE SUBJECT TO TYPICAL VARIATION.			
PROCESS SPECIFICATIONS	SIZE	TYPE	DWG NO.
NEXT ASBY	B	C-	
SCALE:		NONE	
		SS20W/XX	
		SHEET 1	OF 1
			REVISION B2
ECO-MATE SOCKET CONTACT, STAMPED, 20-22AWG, SIZE 20			
Sine Systems - www.amphenol-sine.com 44724 Money Drive Clinton Township, MI 48036			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS20W1F](#)