

SOFIX[®] POWER CABLE ASSEMBLIES

Part of the Metral[®] Backplane Connector Family

OVERVIEW

Higher input/output density and signal speeds demand management of EMC. The Sofix[®] front I/O interconnect system is comprised of right-angle headers and cable plugs that are suitable for the distribution of power and signals.

Sofix[®] connectors are fully shielded down to the PCB level to provide EMC shielding at the sub-rack/front panel level. When used with appropriate cables, the emission level from these links is well below IEC/CISPR 22 and FCC part 15 class B requirements.

Sofix[®] power connectors feature a robust design and are suitable for applications in systems with slot pitch as low as 15mm. The design rules for the Sofix[®] family of I/O connectors are derived from the Metral system (IEC 61076-4-104). As such, the Sofix[®] system can be used as complement to the Metral backplane connector family or applied as dedicated I/O solution.



FEATURES & BENEFITS

- Unique EMC properties
- 10 Amps per power contact
- According to IEC 60950 and UL 1950
- Hot pluggable
- Robust design
- 15mm slot pitch
- RoHS-compliant design

TARGET MARKETS/APPLICATIONS

- Communication
- Instrumentation
- Medical
- Hazardous environments





TECHNICAL INFORMATION

MATERIALS

- Plug
 - Housing: Polybutylene terephthalate (PBT UL94V-0)
 - Terminals: Copper alloy
 - Covers: Zinc alloy
- Header
 - Housing: Liquid crystal polymer (UL94V-0)
 - Terminals: Copper alloy
 - Covers: Zinc alloy
 - Ground spring: Stainless steel

ELECTRICAL PERFORMANCE

- Current rating: 10 A per contact
- Withstanding voltage: 1000V RMS
- Initial insulation resistance: 5000MΩ min.

MECHANICAL PERFORMANCE

- Insertion force: 20 N max.
- Durability: 200 cycles (Telcordia)
- Temperature range: -40°C to +70°C

PART NUMBERS

Description	Part Numbers
Header Right Angle with 15 Amp Filter	72846-204LF
Cable Connector Kit	72824-201LF

SPECIFICATIONS

- Header: GS-12-307
- Cable connector: GS-12-308
- Recommended cable specification:
 - Copper 2.5mm²
 - Overall Ø 1.95mm
 - Total diameter Ø 8.0mm max.
- Packaging specification: GS-14-1093
- Per Telcordia GR1217-CORE, central office requirements

CERTIFICATIONS & APPROVAL

- Underwriters Laboratories Inc. (UL file no. E66906)
- Canadian Standards Association (CSA file no. LR46923)

PACKAGING

- Headers: Tubes
- Header accessories: Bags
- Cable connector components: Bags

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[HM1C16D2J110EBLF](#) [10022805-201LF](#) [72850-101LF](#) [72800-212LF](#) [85988-002LF](#) [85988-003LF](#) [52088-201LF](#)
[52088-203LF](#) [72800-211LF](#) [72814-205LF](#) [72830-201LF](#) [72830-202LF](#) [72830-203LF](#) [72841-202LF](#) [72841-203LF](#)
[72844-201LF](#) [72845-201LF](#) [72846-205LF](#) [72847-203LF](#) [72850-702LF](#) [72850-703LF](#) [72860-201LF](#) [72831-201LF](#)
[72847-202LF](#) [72811-001LF](#) [72849-201LF](#) [10064583-201LF](#) [72800-211RLF](#) [72800-213LF](#) [72830-201RLF](#) [72845-101LF](#) [72814-202LF](#)