




SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



- Material:
- Item ① Terminal lever: Thermoplastic (UL94V-0)
 - Item ② Terminal top housing: Thermoplastic (UL94V-0)
 - Item ③ Terminal back housing: Thermoplastic (UL94V-0)
 - Item ④ Female contact : PhBz Tin Plated.
 - Item ⑤ Spring clamp : Stainless steel
 - Item ⑥ Terminal down housing: Thermoplastic (UL94V-0)

- Electrical: cULus
- Voltage rating: 160 V
 - Current rating: 5.5 A
 - Wire range:
 - Solid wire(AWG): 16-24
 - Stranded wire(AWG): 16-24
 - Wire strip length: 9-10 mm
 - Withstanding Voltage: 1.32 KV
 - Operating temperature: -40°C to +115°C
 - APPROVAL: US

KD xx 1 0 x 0 Axxx G

No. OF POLES
 04: 2x2 POLES
 06: 2x3 POLES
 :
 48: 2x24 POLES

COLOR
 0: BLACK
 5: GREEN (RAL 6018/T)
 6: BLUE
 8: GREY (RAL 7035/D)

G: Pb<40000ppm
 A000: "@" Logo (Standard)
 A00A: "ANYTEK" Mark
 Any special item by customer request.
 please contact sales department.

POLE		2	3	4	5	6	7	8	9	10	11	12
Dim.L		7.70	11.20	14.70	18.20	21.70	25.20	28.70	32.20	35.70	39.20	42.70
Dim.P		3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50
Tol.		±0.15					±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
Dim.L	46.20	49.70	53.20	56.70	60.20	63.70	67.20	70.70	74.20	77.70	81.20	84.70
Dim.P	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50
Tol.		±0.30					±0.40					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KD 3.5mm W/O Flange (Double level) Series										
PART NO.	KDxx10x0AxxxG					DWG NO.	8KD04.01				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance			
		Runner 2010.05.17	Runner 2010.05.17		UNIT: mm			X.	±0.50		
					SCALE: NONE			X.X	±0.30		
					SHEET: 01/01			X.XX	±0.10		
					REV.: B			X°	±1°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KD041050A000G</u>	<u>KD061050A000G</u>	<u>KD081050A000G</u>	<u>KD101050A000G</u>	<u>KD121050A000G</u>	<u>KD141050A000G</u>
<u>KD161050A000G</u>	<u>KD181050A000G</u>	<u>KD201050A000G</u>	<u>KD221050A000G</u>	<u>KD241050A000G</u>	<u>KD261050A000G</u>
<u>KD281050A000G</u>	<u>KD301050A000G</u>	<u>KD321050A000G</u>	<u>KD341050A000G</u>	<u>KD361050A000G</u>	<u>KD381050A000G</u>
<u>KD401050A000G</u>	<u>KD421050A000G</u>	<u>KD441050A000G</u>	<u>KD461050A000G</u>	<u>KD481050A000G</u>	<u>KD201000A000G</u>