






SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




Material:

- Item a :Male contact pin: Copper Tin plated
- Item b :Terminal(housing): Thermoplastic (UL94V-0)
- Electrical: cULus
- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus



SECTION A-A



N = Number of poles  
 Dim A=Nx5.0+3.2  
 Dim B=Nx5.0+0.7  
 Dim C=(N-1)x5.0

	Dim A	Dim B	Dim C
2-6p	±0.20	<sup>+0.15</sup> <sub>-0</sub>	±0.20
6-12p	±0.30	<sup>+0.3</sup> <sub>-0</sub>	±0.30
12-24p	±0.40	<sup>+0.4</sup> <sub>-0</sub>	±0.40

NC xx 7 2 x 0 xxxx G

- |             |                     |   |
|-------------|---------------------|---|
| 02 2 poles  | 0 Black (RAL9005)   | G: Pb<40,000ppm<br><br>any special item by customer request, please contact sales department. |
| 03 3 poles  | 2 Red (RAL3001/D)   |   |
| ... ..      | 3 Orange(RAL2011/P) |   |
| 24 24 poles | 4 Yellow(RAL1018/A) |   |
|             | 5 Green(RAL6018/T)  |   |
|             | 6 Blue (RAL5015/A)  |   |
|             | 8 Grey(RAL7035/D)   |   |

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NC 5.0mm Vertical W/hook holder (100% protected against mismatching)			
PART NO.		NCxx72x0xxxxG		DWG NO.	8NC0003
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2010.08.11	Runner 2010.08.11		Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
				SHEET: 01/01	X° ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>NC0272800000G</u></a>	<a href="#"><u>NC0372800000G</u></a>	<a href="#"><u>NC0472800000G</u></a>	<a href="#"><u>NC0572800000G</u></a>	<a href="#"><u>NC0672800000G</u></a>	<a href="#"><u>NC0772800000G</u></a>
<a href="#"><u>NC0872800000G</u></a>	<a href="#"><u>NC0972800000G</u></a>	<a href="#"><u>NC1072800000G</u></a>	<a href="#"><u>NC1172800000G</u></a>	<a href="#"><u>NC1272800000G</u></a>	<a href="#"><u>NC1372800000G</u></a>
<a href="#"><u>NC1472800000G</u></a>	<a href="#"><u>NC1572800000G</u></a>	<a href="#"><u>NC1672800000G</u></a>	<a href="#"><u>NC1772800000G</u></a>	<a href="#"><u>NC1872800000G</u></a>	<a href="#"><u>NC1972800000G</u></a>
<a href="#"><u>NC2072800000G</u></a>	<a href="#"><u>NC2172800000G</u></a>	<a href="#"><u>NC2272800000G</u></a>	<a href="#"><u>NC2372800000G</u></a>	<a href="#"><u>NC2472800000G</u></a>	