


SIGN	DATE	DESCRIPTION	APPROVER
△	2011.08.24	The dimension is changed from 15.24mm to 15.00±0.20mm	Aaron
△	2011.08.24	The dimension are added	Aaron
△	2011.08.24	The dimension is changed from 23.7mm to 23.6mm	Aaron
△	2011.08.24	The dimension is changed from 15.24mm to 15.00mm	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ③ Short male Contact pin: Copper ,Tin plated
- Item ⑥ Long male Contact pin: Copper ,Tin plated
- Item ⑦ Terminal (housing): Thermoplastic (UL94 V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 
- Critical dimension: ▽

VF xx 71 x 0 xxxx G

Poles	Color	RoHS
04 2x2Poles	0 Black (RAL9005)	Pb<40,000ppm
06 2x3Poles	2 Red (RAL3001/D)	0000 Standard @ Logo
...	3 Orange(RAL2011/P)	000A Standard ANY Logo
48 2x24Poles	4 Yellow(RAL1018/A)	Any special item by
	5 Green(RAL6018/T)	customer request,
	6 Blue (RAL5015/A)	please contact sales
	8 Grey(RAL7035/D)	department.
	9 White(RAL1102)	
	C Green(RAL6018/U)	


N=NUMBER OF CONTACTS

Dimension		TOL				
		2x2P-2x5P	2x6P-2x10P	2x11P-2x15P	2x16P-2x20P	2x21P-2x24P
Dim L	N/2x5.0+2.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim B	(N/2-1)x5.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim C	(N/2-1)x5.0	±0.15	±0.20	±0.25	±0.30	±0.35
Dim D	(N/2-1)x5.0	±0.15	±0.20	±0.25	±0.30	±0.35

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VF-5.00 Series 2x2P-2x24P (Close) Vertical				
PART NO.	VFxx71x0xxxxG		DWG NO.	8VF0006	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Aaron 2011.08.24	Chen Bo 2011.02.21		X. ±0.50
				UNIT: mm	X.X ±0.30
				SCALE: NONE	X.XX ±0.10
				SHEET: 01/01	X° ±1°
				REV.: C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VF0471500000G</u>	<u>VF0671500000G</u>	<u>VF0871500000G</u>	<u>VF1071500000G</u>	<u>VF1271500000G</u>	<u>VF1471500000G</u>
<u>VF1671500000G</u>	<u>VF1871500000G</u>	<u>VF2071500000G</u>	<u>VF2271500000G</u>	<u>VF2471500000G</u>	<u>VF2671500000G</u>
<u>VF2871500000G</u>	<u>VF3071500000G</u>	<u>VF3271500000G</u>	<u>VF3471500000G</u>	<u>VF3671500000G</u>	<u>VF3871500000G</u>
<u>VF4071500000G</u>	<u>VF4271500000G</u>	<u>VF4471500000G</u>	<u>VF4671500000G</u>	<u>VF4871500000G</u>	