



REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
E		PRODUCT DRAWING	FEB2/12	K.L.



**BI-COLOUR LED DETAIL**  
(RED/YELLOW AND GREEN/ORANGE LED'S ARE ALSO AVAILABLE)



**MATERIALS:**  
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC  
FLAMMABILITY RATING UL 94V-0

**CONTACTS:**  
PHOSPHOR BRONZE  
PLATING: 50  $\mu$  [1.27 MICRONS]  
MIN. GOLD ON MATING SURFACES.  
50  $\mu$  [1.27 MICRONS]  
MIN. NICKEL UNDERPLATE  
100  $\mu$  [2.54 MICRONS]  
MIN. MATTE TIN ON CONTACT TAILS.

**SHIELD:**  
COPPER ALLOY  
PLATING: NICKEL WITH PURE-TIN DIPPED PCB TAILS

**AMPHENOL PART NUMBER:** RJHSE-L38X-02

REFER TO AMPHENOL CATALOGUE  
FOR LED COLOUR OPTIONS

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION  
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING  
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

DRAWN PWANG	DATE 05/12/29	Amphenol Canada Corp.		
DESIGNED				
CHECKED CHIGOW	05/12/29			
I. E. APPRD.				
Q. A. APPRD.				
DWG. APPRD.				
ENG. REL. NO.				
REF.				
DIMENSIONS ARE IN INCHES (mm)	CODE ID. NO. 03554			
SCALE	WT.	SURF.	SHEET 1 OF 1	

**Amphenol Canada Corp.**

TITLE  
2 PORT HIGH SPEED RJ45 MODULAR JACK  
LOW PROFILE, 8 POSITION, 8 CONTACTS  
SHIELDED, WITH LEDS, - RoHS COMPLIANT

DWG. DRAWING NO. P-RJHSE-L38X-02 REV. E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[RJHSE-3085](#) [RJHSE-5382-02](#) [RJHSE-5381-08](#) [RJHSE-5380-08](#) [RJHSE-5382-08](#) [RJHSE-7365](#) [RJHSE-7360-08](#)  
[RJHSE-7365-08](#) [RJHSE-7365-02](#) [RJHSE-7361-08](#) [RJHSE-7361-02](#) [RJHSE-7365-04](#) [RJHSE-5385-08](#) [RJHSE-7361](#)  
[RJHSE-5387-04](#) [RJHSE-7361-04](#) [RJHSE-538B-08](#) [RJHSE-5388-08](#) [RJHSE-5388-04](#) [RJHSE-7360-04](#) [RJHSE-](#)  
[5387-08](#) [RJHSE-7060-02](#) [RJHSE-5387-02](#) [RJHSE-5387](#) [RJHSE-5386-08](#) [RJHSE-5386-04](#) [RJHSE-5386-02](#)  
[RJHSE-5386](#) [RJHSE-5388](#) [RJHSE-7065](#) [RJHSE-7360-02](#) [RJHSE-7065-08](#) [RJHSE-7065-02](#) [RJHSE-7060-04](#)  
[RJHSE-7064-08](#) [RJHSE-7064-04](#) [RJHSE-7064-02](#) [RJHSE-7064](#) [RJHSE-7061-08](#) [RJHSE-7061-04](#) [RJHSE-7061-02](#)  
[RJHSE-7061](#) [RJHSE-7060-08](#) [RJHSE-7065-04](#) [RJHSE-5381-A2](#) [RJHSE-5381-A1](#) [RJHSE-538B](#) [RJHSE-538B-02](#)  
[RJHSE-5385-02](#) [RJHSE-5385-04](#) [RJHSE-5380](#) [RJHSE-5381-02](#) [RJHSE-5381-04](#) [RJHSE-5384-08](#) [RJHSE-5384-02](#)  
[RJHSE-538A](#) [RJHSE-3080](#) [RJHSE-3081](#) [RJHSE-338A](#) [RJHSE-3384](#) [RJHSE-3385](#) [RJHSE-5380-02](#) [RJHSE-5481](#)  
[RJHSE-538W-02E](#) [RJHSE-538A-02](#) [RJHSE-538A-04](#) [RJHSE-7360](#) [RJHSE-5380-04](#) [RJHSE-538B-04](#) [RJHSE-](#)  
[5382](#) [RJHSE-5382-04](#) [RJHSE-5388-02](#) [RJHSE-5380A1](#) [RJHSE-5380A8](#) [RJHSE-5386A8](#) [RJHSE-5387A1](#) [RJHSE-](#)  
[5387A2](#) [RJHSE-5387A4](#) [RJHSE-5387A8](#) [RJHSE-5388A1](#) [RJHSE-5388A2](#) [RJHSE-5388A4](#) [RJHSE-5388A8](#)  
[RJHSE-5485](#) [RJHSE-5486](#) [RJHSE-5487](#) [RJHSE-5488](#) [RJHSE-548A](#) [RJHSE-548B](#) [RJHSE-5382A2](#) [RJHSE-](#)  
[5382A4](#) [RJHSE-5382A8](#) [RJHSE-5384A2](#) [RJHSE-5384A4](#) [RJHSE-5385A2](#) [RJHSE-5385A8](#) [RJHSE-5386A1](#)  
[RJHSE-5386A2](#) [RJHSE-5386A4](#) [RJHSE-5481A1](#)