


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



D	Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	
	Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	
	Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no		
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		
	Rated voltage	UL 1977	250V									60V	
C	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)				
	Pollution degree ²⁾	IEC 60664-1	1 (2)										
	Installation category	IEC 60664-1	I										
	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600										
	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C							3A/+40°C	
	Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ³⁾										
	Contact resistance	IEC 60512-2-1	<5mOhm										
	Climatic category	IEC 60668-1	40 / 100 / 56										
	Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F										
	IP degree	IEC 60529	IP 40										
B	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	
	mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles										
	housing material		brass and / or zinc die cast, nickel plated or thermoplast										
	dielectric material		thermoplastic										
	contacts		silver or gold plated, please order contacts separately acc. to drawing M-N 01 015 00XX X (3-8pol) or M-N 01 010 0158 X (12-14pol)										
	termination technique		crimp										
	wire gauge		0,09-1,0mm²			0,09-0,75 mm²	0,09-1,0 mm²	0,09-0,75mm²			0,09-0,25mm²		
	flamability		UL 94 V0										
	locking system		metal screw coupling; tightening torque 0,7 - 1,5 Nm										

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal warranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	14 (14-a)	T 3650 554 U
	12 (12-a)	T 3635 554 U
	8 (08-a)	T 3504 554 U
	7 (07-b)	T 3484 554 U
	7 (07-a)	T 3475 554 U
	6 (6-a)	T 3400 554 U
	5 (05-b)	T 3356 554 U
	5 (05-a)	T 3360 554 U
	4 (04-a)	T 3300 554 U
	3 (03-a)	T 3260 554 U
	2 (Pin 1+3)	T 3200 554 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. DIN EN 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT: 0,026 kg				Zul. Abw./Tolerances: ISO 2768-c		Maßstab / Scale : 2:1		A3		
Prüfmaß / Testdimension						DIN / ISO 13715				
Teileindex / Partindexnumber:										
Bagatelle change:						CUSTOMER DRAWING				
				Gez.	15.06.2021	Male cable connector for cable diameter 4-6mm				
				Drawn	MCARLE					
				Status	Released					
				Gepr.	16.06.2021					
				Checked	MBERTSCH					
				Amphenol Tuchel Industrial GmbH		M HA T 3XXX 554 U				
01	202100006	15.06.2021	MCARLE			Blatt/ Sheet 1				
Index	Änderung/ Description	Datum/ Date	Name			1 Bl.				
						Ers. f. / Replacement for :				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T 3300 554](#)