



DIMENSION


Dim L	N×7.62
Dim A	(N-1)×7.62

N=Number of poles

Poles	Tolerance
4p-8p	±0.20
9p-12p	±0.30
13p-16p	±0.40



SECTION P-P



RECOMMENDED PCB LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	12/01'10	Add is " VDE "	Aaron
△	08/11'11	The tolerance is changed	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- Item 3 Wire guard solder pin:Brass Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

△ Electrical cULus / VDE

- Voltage rating : 300VAC / 750V
- Current rating : 20A / 24A
- Wire range : 0.2-2.5mm²
- Solid wire(AWG) : 12-30
- Stranded wire(AWG) : 12-30
- Torque : 3.5 Lb-In / 0.5 N.m
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV / 3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:
- Critical dimension:

VJ xx 61 x 5 xxxx G

RoHS
Pb<40,000ppm

No. of poles	Color	Code
04 4 CONTACTS	Black (RAL9005)	0000:"@Logo (Standard)
05 5 CONTACTS	Red (RAL3001/D)	000A:"ANYTEK"Logo
...	Orange(RAL2011/P)	Any special item by
16 16 CONTACTS	Yellow(RAL1018/A)	customer request,
	Green(RAL6018/T)	please contact sales
	Blue (RAL5015/A)	department.
	Grey(RAL7035/D)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VJ-7.62 Series 4P-16P Horizontal Solid block (180D wire inlet)-----Without cover						
PART NO.	VJxx61x5xxxxG			DWG NO.	8VJ0312		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
	Shi Jun 2011.08.11	Runner 2011.08.11	Aaron 2009.07.21		UNIT: mm	Tolerance	
					SCALE: NONE	X. ±0.50	
						X.X ±0.30	
						X.XX ±0.10	
						X° ±1°	
				SHEET: 01/01	REV.: C2		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[VJ0461550000G](#) [VJ0561550000G](#) [VJ0661550000G](#) [VJ0761550000G](#) [VJ0861550000G](#) [VJ0961550000G](#)
[VJ1061550000G](#) [VJ1161550000G](#) [VJ1261550000G](#) [VJ1361550000G](#) [VJ1461550000G](#) [VJ1561550000G](#)
[VJ1661550000G](#)