

SIGN	DATE	DESCRIPTION	APPROVER
△	01.12'06	Standard spec is changed.	Marivn
△	02.05'13	Update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item③ Terminal body: Brass(CuZn),Tin plated
- Item④ Terminal screw: Steel Zinc plating "-" slot type
- Item⑤ Wire guard: Stainless steel
- Item⑥ Terminal housing:Thermoplastic (UL94V-0)

△ Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- SAFETY APPROVAL DETAIL: cULus
- Critical dimension: △

VA xx 0 1 x 0 xxxx G


End Stackable
02 02 CONTACTS
03 03 CONTACTS
...
24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- C Green(RAL6018/U)


G RoHS compliant
(lead<4%)
In copper Alloy

0000 "@" Logo
000A "ANY" Logo
...
Any special item by
customer request,
please contact sales
department



N = Number of poles
Dim L=Nx5.0
Dim P=(N-1)x5.0

	Dim L	Dim P
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE	VA- 5.0mm Series						
PART NO.	VAXx01x0xxxxG			DWG NO.	8VA0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Chen Bo 02/05'13	Chen Bo 02/05'13		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHEET: 01/01		X.XX ±0.10
					REV: D		X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VA0201600000G</u>	<u>VA0301600000G</u>	<u>VA0401600000G</u>	<u>VA0501600000G</u>	<u>VA0601600000G</u>	<u>VA0701600000G</u>
<u>VA0801600000G</u>	<u>VA0901600000G</u>	<u>VA1001600000G</u>	<u>VA1101600000G</u>	<u>VA1201600000G</u>	<u>VA1301600000G</u>
<u>VA1401600000G</u>	<u>VA1501600000G</u>	<u>VA1601600000G</u>	<u>VA1701600000G</u>	<u>VA1801600000G</u>	<u>VA1901600000G</u>
<u>VA2001600000G</u>	<u>VA2101600000G</u>	<u>VA2201600000G</u>	<u>VA2301600000G</u>	<u>VA2401600000G</u>	<u>VA0301500000G</u>