



DIM		TOL		
		2P-5P	7P-8P	9P-12P
Dim L	(N-1)X5.08+4.04	±0.20	±0.30	±0.40
Dim P	(N-1)×5.08			

SIGN	DATE	DESCRIPTION	APPROVER
△	01/27`07	The Soldering temperature changed from 245°C to 250°C	Aaron
△	05/05`12	Operating temperature is changed	Runner
△	05/05`12	Lever material is changed	Runner
△	05/05`12	Add the tolerance	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

## Material

- Item ① Solder Pin(Contact pin) : Brass ,Tin plated
- Item ② Spring clamp : Stainless steel
- Item ③ Terminal cover: Thermoplastic ( UL94V-0 )
- Item ④ Terminal housing: Thermoplastic ( UL94V-0 )
- ▲ ● Item ⑤ Lever: Thermoplastic ( UL94 HB )
- Item ⑥ Pad board: Thermoplastic ( UL94V-0 )

## Electrical cULus

- Voltage rating:150V
- Current rating:4A
- Wire range:
- Solid wire(AWG):22-28
- Stranded wire(AWG):22-28
- Wire strip length:6-7mm
- Withstanding Voltage:1.3KV
- ⚠ ● Operating temperature:-40°C to +115°C
- ⚠ ● Soldering temperature:250°C±10°C/5 Sec
- Safety approval : us
- Critical dimension: 


HE xx 20 x 0 0000 G

02	2 POLES	0	Black(RAL9005)	0000	Standard @ Logo	RoHS compliant
03	3 POLES	3	Orange(RAL2011/P)	000A	Standard ANY Logo	(lead<4%)
...	...	5	Green(RAL6018/T)		Any special item by	In copper Alloy
12	12 POLES	6	Blue(RAL5015/A)		customer request,	
		8	Grey (RAL7004/P)		please contact sales	
					department.	

# ANYTEK

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HE 5.08 SERIES With lever						
PART NO.	HExx20x00000G			DWG NO.	8HE0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Runner 2012.05.05	Marvin 2006.07.03		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: C	X.XX ±0.10	
						X° ±1°	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HE0220400000G](#) [HE0320400000G](#) [HE0420400000G](#) [HE0520400000G](#) [HE0620400000G](#) [HE0720400000G](#)  
[HE0820400000G](#)