


Copied of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



D	Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14
	Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
	Contact arrangement	IEC 60130-9 ¹⁾			-			-			-	
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)	300 V (63 V)	100 V (32 V)	300 V (63 V)	100 V (32 V)				150 V (32 V)	
E	Rated voltage	UL 1977	250 V								60 V	
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (840 V)	1200 V (500 V)	1500 V (840 V)	1200 V (500 V)						
	Pollution degree ²⁾	IEC 60664-1	1 (3 ³⁾)									
	Installation category	IEC 60664-1	I									
C	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600									
	Current rating	IEC 60512-5-2 UL 1977	5A/+40°C/+104°F								3A/+40°C/+104°F	
	Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ⁴⁾									
	Contact resistance	IEC 60512-2-1	<5m Ohm									
B	Climatic category	IEC 60668-1	40 / 100 / 56									
	Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F									
	IP degree	IEC 60529	IP 40 (in mated condition)									
	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	50N	55N	60N	50N			
A	Mechanical operation	IEC 60512-9-1	silver ≥500 mating cycles gold ≥1000 mating cycles									
	Housing material		brass and / or zinc die cast, nickel plated									
	Dielectric material		thermoplastic									
	Contacts		silver or gold plated, please order contacts separately acc. to drawing M-N 01 015 00XX X (3-8pol) or M-N 01 010 0158 X U (12-14pol)									
	Termination technique		crimp									
	Wire gauge		2-6 pol (exclusive 5S): 0,09-1,0mm ² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm ² / 28-20 AWG								0,09-0,25mm ² / 28-24 AWG	
	Flamability		UL 94 VO									
	locking system	IEC 60130-9 DIN EN 61076-2-106	metal screw coupling; tightening torque 0,7Nm									

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ designed acc. pollution degree 2; can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
⁴⁾ under operating conditions >10⁸ Ohm

All technical data have been measured in a laboratory environment and can be different during pratical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
Parts according to directive 2002/95/EG (RoHS).

	14 (14-a)	T 3650 551 U
	12 (12-a)	T 3635 551 U
	8 (08-a)	T 3504 551 U
	7 (07-b)	T 3484 551 U
	7 (07-a)	T 3475 551 U
	6 (06-a)	T 3400 551 U
	5 (05-b)	T 3356 551 U
	5 (05-a)	T 3360 551 U
	4 (04-a)	T 3300 551 U
	3 (03-a)	T 3260 551 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT: g				Zul. Abw./Tolerances:		Maßstab / Scale : 2:1		A3			
Prüfmaß / Testdimension						CUSTOMER DRAWING					
Teileindex Partindexnumber						Kabelstecker gerade male cable connector					
				2015	Datum/Date						Name
				Gez.	06.03.						Mohrlang
				Drawn							
				Gepr.							
				Checked							
				Amphenol-Tuchel Electronics GmbH			M HA T 3XXX 551 U				Blatt/ Sheet 1
02	201500171	25.06.14	IM				Ers. f. / Replacement for : M-HA T 3XXX 551 U Rev01				
Index	Änderung/Description	Datum/Date	Name								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T3400-551](#)