





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal housing : Thermoplastic (UL94V-0)
- Terminal housing : Brass , Ni plated
- Wire guard solder pin : Brass ,Tin plated
- Terminal screw: Steel Zinc plating “-” slot type

Electrical cULus


- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus



P.C.B. LAYOUT

TP 24 01 x 1 xxxx G

- 0 Black
- 5 Green (RAL6018/T)
- 6 Blue
- 8 Grey (RAL7035/D)
- 0000:"@“Logo (Standard)
- 000A:"ANYTEK“Logo
- Any special item by customer request, please contact sales department.
- Pb < 40,000ppm (RoHS)

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO.,LTD			
TITLE		TP 5.0mm 24P 成品圖					
PART NO.		TP2401x1xxxxG		DWG NO.		8TP0006	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Aaron 2009.12.01	xionghaitao 2006.02.09		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHEET: 01/01		X.XX ±0.10
					REV.: B		X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TP2401510000G](#)