

SIGN	DATE	DESCRIPTION	APPROVER
△	6/24'06	Torque standard is changed from 3.5Lb-In to 1.7Lb-In	Marvin
△	11/08'08	Body 加壓設計變更	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material



- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating “-” slot type
- Item c Female contact: PhBz, Tin or Au plated.
- Item d Terminal(housing): Thermoplastic (UL94V-0)

Electrical


- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- △ Torque(Lb-In): 1.7
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety approval: 

TT xx 01 x 0 xxxx G

02	2 CONTACTS	0	Black (RAL9005)	0000	Standard @ Logo	RoHS
03	3 CONTACTS	2	Red (RAL3001/D)	000A	Standard ANY Logo	Pb<40,000ppm
...	...	3	Orange(RAL2011/P)	Any special item by customer request, please contact sales department.		
24	24 CONTACTS	4	Yellow(RAL1018/A)			
		5	Green(RAL6018/T)			
		6	Blue (RAL5015/A)			
		8	Grey(RAL7035/D)			



N=Number of contacts



Section C-C

N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.25	±0.15
13-18p	±0.30	±0.20
19-24p	±0.40	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TT - 5.0mm Series Stackable type							
PART NO.	TTxx01x0xxxxG			DWG NO.	8TT0001			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
	Marvin 2006.08.30	Marvin 2006.08.30	Marvin 2006.10.04				X. ±0.50	X.X ±0.30
					UNIT: mm	X.XX ±0.10		
					SCALE: NONE	X° ±1°		
				SHEET: 01/01	REV: E			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TT0201800000G</u>	<u>TT0301800000G</u>	<u>TT0401800000G</u>	<u>TT0501800000G</u>	<u>TT0601800000G</u>	<u>TT0701800000G</u>
<u>TT0801800000G</u>	<u>TT0901800000G</u>	<u>TT1001800000G</u>	<u>TT1101800000G</u>	<u>TT1201800000G</u>	<u>TT1301800000G</u>
<u>TT1401800000G</u>	<u>TT1501800000G</u>	<u>TT1601800000G</u>	<u>TT1701800000G</u>	<u>TT1801800000G</u>	<u>TT1901800000G</u>
<u>TT2001800000G</u>	<u>TT2101800000G</u>	<u>TT2201800000G</u>	<u>TT2301800000G</u>	<u>TT2401800000G</u>	<u>TT0201000000G</u>