


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



	Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19
	Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a
	Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no			
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		60 V (32 V)	
	Rated voltage	UL 1977	250V								60V			
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)					
	Pollution degree ²⁾	IEC 60664-1	1 (2)											
C	Installation category	IEC 60664-1	I											
	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600											
	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C			
	Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ³⁾											
	Contact resistance	IEC 60512-2-1	<5mOhm											
	Climatic category	IEC 60668-1	40 / 100 / 56											
	Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F											
	IP degree	TEC 60529	IP 40											
B	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
	mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
	housing material		brass and / or zinc die cast, nickel plated or thermoplast											
	dielectric material		thermoplastic											
	contacts		silver or gold plated											
	termination technique		solder											
	wire gauge		≤0,5mm ² / 20 AWG									≤0,35mm ² / 22 AWG		
	flamability		UL 94 V0											
	locking system		metal screw coupling; tightening torque 0,7 - 1,5 Nm											

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	19 (19-a)	Ag	T 3691 004 U
	14 (14-b)	Ag	T 3671 004 U
	14 (14-a)	Ag	T 3651 044 U
	12 (12-a)	Ag	T 3636 044 U
	8 (08-a)	Ag	T 3505 004 U
	7 (07-b)	Ag	T 3485 004 U
	7 (07-a)	Ag	T 3476 004 U
	6 (6-a)	Ag	T 3401 004 U
	5 (05-b)	Ag	T 3361 004 U
	5 (05-a)	Ag	T 3361 048 U
	4 (04-a)	Ag	T 3301 004 U
	3 (03-a)	Ag	T 3261 004 U
	2 (Pin 1+3)	Ag	T 3201 004 U
	2 (Pin 1+3)	Ag	T 3201 048 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. DIN EN 61076-2-106)	contact plating	Part number

Gewicht (errechnet) / Calc WT : 34,46 g				Zul. Abw./Tolerances : ISO 2768-c		Maßstab / Scale : 2:1		A3							
Prüfmaß / Testdimension						CUSTOMER DRAWING									
Teileindex / Partindexnumber:															
Bagatelle change: 23.02.2021 MCARLE						Female cable connector PG7, cable diameter 4-6mm									
				Gez. 30.11.2020											
				Drawn MCARLE											
				Status Released											
				Gepr. 10.02.2021											
				Checked MBERTSCH											
				Amphenol Tuchel Industrial GmbH				M DA T 3XXX 004+048 U		Blatt/ Sheet 1					
										1 Bl.					
02		202000083		05.02.2021		MCARL									
Index		Änderung/Description		Datum/Date		Name		Ers. f. / Replacement for : M-DA T 3XXX 004+048 U Rev01							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T 3476 048](#)