


10134355-XXXXLF

- LF: Lead Free, RoHs compliant, see note
XXX : Color ref or/and version



Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

PN	Colour	Version
10134355-001LF	grey	
10134355-002LF	blue	
10134355-003LF	yellow-green	

TECHNICAL DATA / DIMENSIONS

Dimensions	
Width mm	5.0
Length mm	77.0
Height mm	52.0
Mounting type (EN 60715)	Omega TH35
Technical data	
Maximum load current	24A (12A + 12A)
Insulating material	PA
Self-extinguishing degree acc. to UL94	V0
Rated surge voltage	6kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal Voltage	400V
Nominal Current	12A
Connection data	
Conductor cross-section solid min/max	0.50 / 2.5 mm ²
Conductor cross-section stranded min/max	0.50 / 2.5 mm ²
AWG min/max	24-12AWG
Max conductor cross-section stranded with ferrule with plastic sleeve	2.5 mm ² / L=10 mm
Stripping length	max 8 mm
Screw	M2.6
Tightening torque	0.5Nm / 4.0 Lb-In

ACCESSORIES

Item	Description
Marking	
10134398-001LF	Blank single-digit marking tags
10134398-002LF + 10134398-011LF	Printed single-digit marking tags numbered : 1÷0
10134398-012LF + 10134398-041LF	Printed single-digit marking tags with letter: A÷Z
10134399-001LF	Marking tag adapter
10134400-001LF	Blank Marking tags

DIN RAIL system - Mounting and Installation material

10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm
10134391-001LF	Fast-snap End Bracket for TH35 Omega rail

Additional items

10134361-001LF	End Plate for Terminal Blocks two stage XDV 2,5
10134361-002LF	End Section for Terminal Blocks two stage XDV 2,5
10134364-001LF	Spacer for Terminal Blocks two stage XDV
10134273-001LF	Jumper bar 2 poles, pitch 5,1mm J2,5
10134273-002LF	Jumper bar 3 poles, pitch 5,1mm J2,5
10134273-003LF	Jumper bar 24 poles, pitch 5,1mm J2,5
10134271-001LF	Ratchet Cutting Tool for jumper bar J2,5 -orange
10134276-001LF	Red test plug adapter
10134276-002LF	Black test plug adapter
10134365-001LF	Female terminal block - 90°- pitch 5,08mm – All poles

spec ref		dr Aymeric Saudy		09-07-2015		projection		size A3		scale 1:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Aymeric Saudy		09-07-2015				mm			
ISO 406				chr									
ISO 1101				appr Aymeric Saudy		09-07-2015		product family DIN Terminal Block		ecn no		rel level	
surface ✓ ISO 1302		linear		0X ± 0,3 0XX ± 0,1 0XXX ± 0,05				title Two stage SCREW Terminal Block XDV 2,5 vertical		dwg no 10134355		rev A	
		angular		0° ± 2°		www.fcicom		cat. no.		- Product customer drawing		sheet 1 of 1	

APPROVALS



AWG 24-12 – 300V – 12A

EN60947-7-1

EN61984

2.5mm² – 400V – 12A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10134355-002LF](#) [10134355-001LF](#) [10134355-003LF](#)