







Copyright FCI.

PRODUCT NUMBER
SEE TABLE



RECOMMENDED PC DIMENSIONS
COMPONENT SIDE




mat'l code NOTE 1 & 2				tolerance unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
rev	ecn no.	dr	date	linear	.0 ± .30 .00 ± .20 .000 ± .10	projection	title	USB+POWER RECEPTACLE ASSY	
				angles	0° ± 3°				
		dr	Nick. Zhang	6/15/15	unit	MM	product family	USB	code
		engr	Nick. Zhang	6/15/15	size	dwg no.			NT
		chr	Qing. Li	6/15/15	scale	2:1			sheet
		appd	Tim. Yao	6/15/15					1 OF 4
sheet	revision	A							
index	sheet	1~4							




Copyright FCI.


PRODUCT NUMBER
SEE TABLE



KEY POSITION 1
10135709-10X
10135709-50XLF
10135709-80XLF





KEY POSITION 2
10135709-20X
10135709-60XLF
10135709-00XLF



KEY POSITION 3
10135709-30X
10135709-70XLF
10135709-90XLF

ABOVE ASSEMBLIES ARE SHOWN LNLY FOR
KEY INFORMATION, FOR ASSEMBLY INFORMATION
AND DIMENSIONS SEE PREVIOUS SHEETS



mat'l code NOTE 1 & 2		tolerance unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
rev	ecn no.	dr	date	linear	.0 ± .30 .00 ± .20 .000± .10	projection	title
				angles	0° ± 3°		USB+POWER RECEPTACLE ASSY
		dr	Nick. Zhang	6/15/15	unit	MM	product family USB
		engr	Nick. Zhang	6/15/15	scale	A3	code NT
		chr	Qing. Li	6/15/15	size	10135709	sheet 2 OF 4
		appd	Tim. Yao	6/15/15	scale	2:1	
sheet	revision	A					
index	sheet	1~4					



Copyright FCI.


NOTES:




1. MATERIAL:
HOUSING: HIGH TEMP ENGINEERING PLASTIC UL 94V-0
SHIELDS: HIGH STRENGTH COPPER ALLOY, PLATING: TIN/LEAD OR IN OVER NICKEL.
TERMINALS: HIGH STRENGTH COPPER ALLOY, PLATING: NICKEL UNDERPLATING
CONTACT AREA: 30 GXT MIN.
TAIL AREA: TIN/LEAD OR MATT TIN.
2. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994.
3. USB SETION CONFORMS TO USB 2.0 SPECIFICATION.
4. MATTING SEQUENCE WHEN MATED WITH USB+POWER PLUG PRODUCT NUMBER 74233-XXX
5. CURRENT RATING IS 1.5 AMP PER CONTACT FOR THE STANDARD USB SECTION AND 3 OR 5 AMPS
PER CONTACT FOR THE POWER SECTION WITH ALL CONTACTS POWER (SEE PART NUMBER TABLE), SEE GS-12-130
FOR PRODUCT TEST AND PERFORMANCE INFORMATION.
6. P/N 'S WITH SUFFIX "LF" ARE LEAD FREE P/N'S
7. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATION AS DESCRIBED IN GS-22-008
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TERMERATURE FOR 40 SECONDS IN A
CONVECTION, INFRO-RED OR VAPOR PHASE REFLOW OVEN.
9. THIS PRODUCT IS MADE UNDER LICENSE OF IBM U.S. PATENT NO.6334793



CONTACT NUMBER	PRODUCT DASH NUMBER 10135709-			
	-10X/50XLF /80XLF	-20X/60XLF /00XLF	-30X/70XLF /90XLF	MATING SEQ.
1	VCC	VCC	VCC	2
2	- DATA	- DATA	- DATA	3
3	+ DATA	+ DATA	+ DATA	3
4	GROUND	GROUND	GROUND	2
5	12V GROUND	24V GROUND	5V GROUND	2
6	12V	24V	5V	3
7	12V	24V	5V	3
8	12V GROUND	24V GROUND	5V GROUND	2
SHELL	SHIELD	SHIELD	SHIELD	1

mat'l code NOTE 1 & 2				tolerance unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
rev	ecn	no.	dr	date	linear	.0 ± .30	projection	title	
						.00 ± .20		USB+POWER RECEPTACLE ASSY	
						.000± .10			
					angles	0° ± 3°			
			dr	Nick. Zhang	6/15/15	unit	MM	product family	USB
			engr	Nick. Zhang	6/15/15	size	dwg no.	code	
			chr	Qing. Li	6/15/15	scale	A3	10135709	
			appd	Tim. Yao	6/15/15			sheet	
sheet	revision	A						3 OF 4	
index	sheet	1~4							



mat'l code NOTE 1 & 2				tolerance unless otherwise specified				CUSTOMER COPY		<div> www.fciconnect.com</div>			
rev/encl no.		dr		date		linear		.0 ± .30		projection		title	
								.00 ± .20				USB+POWER	
								.000± .10				RECEPTACLE ASSY	
				angles		0° ± 3°							
		dr		Nick Zhang		6/15/15		unit		product family USB		code	
		engr		Nick Zhang		6/15/15		MM		size dwg no.		NT	
		chr		Qing Li		6/15/15		scale		A3		sheet	
		appd		Tim Yao		6/15/15		2:1		10135709		4 OF 4	
sheet revision		A											
index sheet		1~4											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10135709-601LF](#) [10135709-501LF](#)