




Model_name: 10pos_Recpt_Assy Drawing_name: 11828c_revA Model_type:


**METRIC**

TAPE AND REEL PACKAGING




*5MM RECEP 10 POSITION TAPE AND REEL SHOWN

POS	TAPE WIDTH
10	24.00 +/- 0.30 MM
20	32.00 +/- 0.30 MM
30	32.00 +/- 0.30 MM
40	44.00 +/- 0.30 MM
50	56.00 +/- 0.30 MM
60	56.00 +/- 0.30 MM
70	56.00 +/- 0.30 MM



KAPTON TAPE			
POS	LENGTH	WIDTH	THICKNESS
10	5 MM	3.3 MM	0.05 MM
20	5 MM	3.3 MM	0.05 MM
30	15 MM	3.3 MM	0.05 MM
40	15 MM	3.3 MM	0.05 MM
50	15 MM	3.3 MM	0.05 MM
60	15 MM	3.3 MM	0.05 MM
70	15 MM	3.3 MM	0.05 MM

Protective Cap
- Available in 10 - 60 POS



Model_name: ReceAssy10pos_withDOT Drawing_name: 11828c_revA Model_type:

METRIC

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF AMPHENOL INTERCON SYSTEMS AND MAY NOT BE DISCLOSED, REPRODUCED OR OTHERWISE USED WITHOUT WRITTEN PERMISSION

ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5M-2009
ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED

THIRD ANGLE PROJECTION

INSPECTION
◇ FIRST PIECE
△ SPC
○ IN-PROCESS

TOLERANCES UNLESS SPECIFIED OTHERWISE
1PLC ±0.3
2PLC ±0.13
3PLC ±0.050
ANGLES ±1°

MATERIAL 1
FINISH 2

Amphenol
Inter-Con
Systems

AMPHENOL INTERCON SYSTEMS INC.
Etters, PA 17319

NAME
LYNX RECEPTACLE ASSEMBLY

SIZE B
PROD CODE 445
DRAWING NUMBER C- 11828
REV A

SCALE 10:1
CUSTOMER
SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[11828-2DA](#) [11828-2BA](#) [11828-2AA](#) [11828-2CA](#) [11828-2EA](#) [11828-2FA](#) [11828-1FA](#) [11828-1BA](#)

FCI / Amphenol:

[11828-1EA](#)