





REV	ECN	APP'D
-	5814	JT 4-13-06



- NOTES:
1. PERFORMANCE:
- A) MEETS PERFORMANCE AND ENVIRONMENTAL REQUIREMENTS OF MIL-T-81714/1
 - B) MODULES ARE TO BE MOUNTED INTO RACK ASSEMBLY M81714/5 OR/16 OR COMMERCIAL EQUIVALENT.
 - C) DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS AT SEA LEVEL, 200 VRMS AT 100,000 FEET.
 - D) OPERATING TEMPERATURE: -65 C TO 200 C.
 - E) CURENT RATING: 5 AMPS
 - F) VIBRATION AND SHOCK: MIL-T-81714 PARAGRAPH 3.5.5 AND 3.5.8
2. MATERIALS:
- A) HOUSING - POLYETHERIMIDE, COLOR: BLACK.
 - B) GROMMET - SILICONE ELASTOMER, COLOR: BLUE
 - C) INTERNAL CONTACTS - COPPER ALLOY, GOLD PLATED
 - D) CONTACT RETAINERS - STAINLESS STEEL.

APCD P/N	SUPPLIED					MARKING		CLASS
	QTY.	MIL. P/N	APCD P/N	QTY.	APCD P/N	APCD QPL NO.	MIL. NO	
TJM122604	--	--	--	--	--	TJM122704	M81714/1-DB3	D
TJM122704	11	M39029/1-100	CNP068000	2	CNA032401			

<div>DIMENSIONS</div> <div>ANSI Y14.5M</div> <div>UNITS: INCHES</div> <div>Pro/E FILE</div>	<div>TOLERANCES</div> <div>.XX ±0.01</div> <div>.XXX ±0.005</div> <div>ANGLES ±2.0°</div>	<div>PROJECTION</div> <div></div>	<div>Amphenol Pcd</div> <div>SPECIFICATION DRAWING</div> <div>DRWN</div> <div>A. SWEEZEY03/09/06</div>		<div>TITLE</div> <div>TERMINAL JUNCTION</div> <div>MODULE</div> <div>SZ 22 FEEDBACK, DB3</div>				
<div>ORIGINAL</div> <div></div>	<div>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., PEABODY, MA</div>		<div>ENGR</div> <div>R. SWAINE03/01/06</div>		<div>SIZE</div> <div>B</div>	<div>DWG NO.</div> <div>TJM122604</div>		<div>REV</div> <div>-</div>	
			<div>APPD</div> <div></div>						
					<div>CODE:</div> <div>58982</div>	<div>SCALE:</div> <div>3:1</div>	<div>SHEET</div> <div>1 OF 1</div>		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJM122704](#) [TJM122604](#)