


REV	ECN	APP'D
-	6588	<i>gvt 9/28/10</i>



NOTES:



1. MATERIALS:

HOUSING: POLYETHERIMIDE, COLOR BLACK
 GROMMET: SILICONE ELASTOMER, COLOR BLUE
 INTERNAL CONTACT: COPPER ALLOY, GOLD PLATED,
 PER MIL-DTL-45204, TYPE I, GRADE C, CLASS I
 50 MICROINCH MIN. OVER NICKEL PER SAE-AMS-QQ-N-290,
 CLASS 1, 50/30 MICROINCH MIN.
 CONTACT RETAINER: STAINLESS STEEL

2. SPLICE ACCEPTS (4) MATING M39029/1-100 CONTACTS (INCLUDED)

3. PART COMPLIES TO ALL REQUIREMENTS PER SAE-AS81714.

4. RESISTOR: 47.5Ω , 1/8W, $\pm 1\%$, RLR05C47R5FS

<div>DIMENSIONS</div> <div>ANSI Y14.5M</div> <div>UNITS: INCHES</div> <div>Pro/E FILE</div>	<div>TOLERANCES</div> <div>.XX ±0.01</div> <div>.XXX ±0.005</div> <div>ANGLES ±2.0°</div>	<div>PROJECTION</div> <div></div>	<div>Amphenol Pcd</div> <div>SPECIFICATION DRAWING</div> <div>ENGR</div> <div>M. DiGIACOMO 09/07/10</div>	<div>TITLE</div> <div>WIRE SPLICE, ELECTRONIC RESISTOR, 47.5Ω, 1/8W, 1% SIZE 22</div>		
<div>ORIGINAL</div> <div></div>	<div>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD BEVERLY, MA, USA</div>		<div>CHKD</div> <div>R. Newman 9/28/10</div> <div>APPD</div> <div>Jahon 9/28/10</div>	<div>SIZE</div> <div>A</div>	<div>DWG NO.</div> <div>TJSE22842_C</div>	<div>REV</div> <div>-</div>
				<div>CODE:</div> <div>58982</div>	<div>SCALE:</div> <div>2:1</div>	<div>SHEET 1 OF 1</div>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJSE22842](#)