

Conan® 1.00mm Connector System

SECURE, HIGH SPEED DESIGN FOR HARSH ENVIRONMENTS

Amphenol's Conan® 1.00mm is a mezzanine connector designed for industrial applications and harsh environments. Its unique design with an audible "click" sound enhances the security and ease of use.

- New right angle configuration in 4 pin counts
- Right angle configurations has compact size of 8.5mm depth and 5.3mm height on PCB after mating
- Enables perpendicular stacking application



FEATURES

- Vertical configuration
 - 9 to 69 positions
 - 4.15mm to 7.0mm stack heights increment
- Right angle configuration
 - 31, 41, 51, 69 position increment
- Vertical housing and terminal profile guarantees support of up to 5Gb/s
- Vertical versus vertical mating configuration
- Vertical receptacle versus RA header mating configuration
- Audible "click" sound during mating
- Polarization feature of housing
- Multiple packaging options available
- Locating pegs option
- Metal hold down option
- RoHS compliant and lead-free

BENEFITS

- Comprehensive range of sizes and stack heights support diverse electronic packaging schemes
- Comprehensive solution to satisfy all customers needs
- Compatible with PCIe® Gen high speed performance on selected stack heights
- Useful for parallel board stacking application
- Useful for perpendicular stacking application
- Ensures secure mating interconnection
- Prevents mismating
- Meets various feeding processing needs
- Facilitates ease and accuracy during manual assembly
- Enables better retention on to the PCB
- Meets environmental, health, and safety requirements

TECHNICAL INFORMATION

MATERIAL

- Contact Base Metal
 - Header: Phosphor Bronze
 - Receptacle: Copper Alloy, High Spring
- Contact Area Finish: Gold or GXT®
- Solder Tail Area: Pure Tin over 1.27µm Nickel
- Housing Material: Cream-colored LCP (UL94V-0)

ELECTRICAL PERFORMANCE

- Insulation Resistance: 1000MΩ min.
- Contact Resistance: 30MΩ max.
- Withstanding Voltage: 500VAC RMS 60Hz
- Current Rating: 1.0A continuous (per contact, all contacts powered)
- Signal Integrity (differential pairs, connector only)
- Impedance: 100Ω ± 10 @ 50 ps edge (10–90%)
- Insertion Loss: < 1.5dB up to 5GHz
- NEXT: ≤3.5% for a 50 ps edge (10–90%)
- FEXT: ≤2.5% for a 50 ps edge (10–90%)

MECHANICAL PERFORMANCE

- Mating Force: 125g per contact max.
- Unmating Force: 25g per contact min.
- Retention Force (connector to PCB): 44N min.
- Contact Wipe: 0.64mm
- Durability: 30 mating cycles

ENVIRONMENTAL

- IMFG per EIA 364–65 class 2a without SO2, 20 days mated
- High Temperature Life: 105°C

SPECIFICATIONS

- Product Specification: GS-12-006

PACKAGING

- Tape and reel with vacuum pickup caps

TARGET MARKETS/APPLICATIONS



Communications and Networking Equipment



Electronic Security
Energy Controller/Module/Display
Machine-to-Machine (M2M) Office Equipment
Point-of-Sale Equipment, Scanning
Portable Meter/Instrument



Medical Diagnostics

PART NUMBER SELECTOR

VERTICAL

Find part number details using the search box on www.amphenol-cs.com

919 — T — C — W — X — Y — ZZ — LF — Lead-free

Type	T
Header with no pegs	0
Header with pegs	1
Receptacle with no pegs	2
Receptacle with pegs	3

Pick And Place Cap or Tape	C
Without cap or tape	0
With cap	1
With tape (receptacle only)	2

Packaging	W
Tube	2
Pressure sealed tape & reel	3

Header Height	Receptacle Height	Mated Height	+100 -008 [+.25] [-.20]	Y
0.43 [.80]	.129 [3.28]	.163 [4.15]		1
0.48 [1.23]	See Y = 1 for all receptacles	.177 [4.50]		2
0.68 [1.73]		.197 [5.00]		3
.107 [2.72]		.236 [6.00]		4
.1465 [3.721]		.276 [7.00]		5


Plating	X
15µin/.38µin. GXT®	1

Number of Positions	ZZ
9	09
11	11
15	15
21	21
25	25
31	31
41	41
51	51
69	69

Recommended packaging combinations:

For production: Connector with pick and place cap packaged in tape and reel (XXXX1-3XXXX) For proto-typing: Connector without pick and place cap packaged in tubes (XXXX0-2XXXX) For commercial applications see print 10118744

MODULE




Mated connector max. width: 5.59mm

RIGHT ANGLE

Description	Part Numbers
Conan® Right Angle Header, 31 positions	10138400-111131LF
Conan® Right Angle Header, 41 positions	10138400-111141LF
Conan® Right Angle Header, 51 positions	10138400-111151LF
Conan® Right Angle Header, 69 positions	10138400-111169LF
Conan® Right Angle receptacle, 11 positions	10180999-211111LF
Conan® Right Angle receptacle, 31 positions	10180999-211131LF

Find part number details using the search box on www.amphenol-cs.com



BASICSCONAN0325E44

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[91910-21441LF](#) [91930-21141LF](#) [91930-21151LF](#) [91910-21415LF](#) [91911-31115LF](#) [91911-31521LF](#) [91910-21351LF](#) [91930-21169LF](#) [91931-31169LF](#) [91910-21421LF](#) [91921-31125LF](#) [91920-21121LF](#) [91931-31141LF](#) [91911-31421LF](#) [91910-21425LF](#) [91930-21115LF](#) [91931-31115LF](#) [91930-21111LF](#) [91930-21109LF](#) [91921-31141LF](#) [91910-21541LF](#) [91900-21115LF](#) [91910-21151LF](#) [91910-21125LF](#) [91911-31531LF](#) [91910-21551LF](#) [91910-21531LF](#) [91910-21521LF](#) [91910-21525LF](#) [91910-21115LF](#) [91910-21111LF](#) [91900-21141LF](#) [91910-21469LF](#) [91911-31441LF](#) [91910-21109LF](#) [91901-31141LF](#) [91900-21221LF](#) [91910-21131LF](#) [91910-21369LF](#) [91921-31121LF](#) [91930-31169LF](#) [91931-32131LF](#) [91911-32569LF](#) [91910-21511LF](#) [91910-21515LF](#) [91920-21131LF](#) [91921-31131LF](#) [91910-21411LF](#) [91930-21131LF](#) [91921-31115LF](#) [91910-21431LF](#) [91931-31131LF](#) [91931-31121LF](#) [91930-21125LF](#) [91901-31269LF](#) [91910-21225LF](#) [91921-31169LF](#) [91910-21409LF](#) [91920-21169LF](#) [91930-21121LF](#) [91900-21131LF](#) [91910-21141LF](#) [91901-31125LF](#) [91910-21169LF](#) [91901-31541LF](#) [91910-21509LF](#) [10118744-1133109LF](#) [10118744-1133125LF](#) [10118744-1133141LF](#) [10118744-1133225LF](#) [10118744-1133231LF](#) [10118744-1133269LF](#) [10118744-1133351LF](#) [10118744-1133415LF](#) [10118744-1133421LF](#) [10118744-1133441LF](#) [10118744-1133451LF](#) [10118744-1133509LF](#) [10118744-1133515LF](#) [10118744-1133541LF](#) [10118744-3133109LF](#) [10118744-3133121LF](#) [10118744-3133141LF](#) [10118744-1133409LF](#) [10118744-1133521LF](#) [10118744-1133121LF](#) [10118744-1133315LF](#) [10118744-1133131LF](#) [10118744-3133115LF](#) [10118744-3133151LF](#) [10118744-1133215LF](#) [10118744-1133251LF](#) [10118744-1133325LF](#) [10118744-3133169LF](#) [91900-21109LF](#) [91900-21111LF](#) [91900-21121LF](#) [91900-21125LF](#) [91900-21151LF](#) [91900-21169LF](#)